



Durable and bright

Philips LED DuraSlim Downlight provides a slim and non-instrusive fitting ideal for rooms with low false ceilings

Easy to experience

• Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

Light effect

- · Bright light with uniform distribution
- Durable synthetic diffuser for uniform light and reduced glare

Premium quality

· Durable and impact resistant die-cast aluminum housing

Durability

· Long life span up to 50,000 hours

Highlights

Suitable for low ceilingsSlim design Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

Durable synthetic diffuser for uniform light and reduced glare

Provides a soft glow for relaxation and focus without distracting glare.

Durable and impact resistant die-cast aluminum housing

The die-cast aluminum housing of this item adds to a cultivated and refined contemporary atmosphere.

Long life span up to 50,000 hours



Philips LED technology extends your product's lifetime up to 50,000 hours.

Specifications

Design and finishing

Color: WhiteMaterial: Metal

Durability

Nominal lifetime: 35.000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- · Remote control included: No

Light characteristics

Beam angle: 120 degree(s)Color rendering index (CRI): 80

· Color temperature: 4000 K

Miscellaneous

• Especially designed for: Living Room

EyeComfort: Yes

Product dimensions and weight

Net weight: 0.215 kg
Overall height: 10 mm
Overall length: 160 mm
Overall width: 160 mm

• Recessed Ceiling cutout: 14.5 cm x 14.5 cm

Service

· Warranty: 2 year(s)

Technical specifications

· Diameter: 160 mm

· Total lumen output fixture: 1260

Light color: 4000Mains power: 220-240

• Fixture dimmable: No

• Wattage bulb included: 12

• IP code: IP20 | Finger-protected

 Class of protection: Class II - Double Insulated

Packaging dimensions and weight

• EAN/UPC - product: 8718696553626

Net weight: 0.18 kgGross weight: 0.24 kg

Height: 16.5 cmLength: 16 cm

• Width: 4.5 cm



Issue date: 2025-09-03 Version: 0.444 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N V