

PHILIPS

Downlight

Functional

DuraSlim

White

8718696690826



Durable and bright

Philips LED DuraSlim Downlight provides a slim and non-intrusive fitting ideal for rooms with low false ceilings

Easy to experience

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

Light effect

- Bright light with uniform distribution
- Durable synthetic diffuser for uniform light and reduced glare

Premium quality

- Durable and impact resistant die-cast aluminum housing

Durability

- Long life span up to 50,000 hours

Highlights

Suitable for low ceilings Slim design Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.


Durable synthetic diffuser for uniform light and reduced glare

Provides a soft glow for relaxation and focus without distracting glare.

Durable and impact resistant die-cast aluminum housing

The die-cast aluminum housing of this item adds to a cultivated and refined contemporary atmosphere.

Long life span up to 50,000 hours



Philips LED technology extends your product's lifetime up to 50,000 hours.

Specifications

Design and finishing

- Color: White
- Material: Metal

Durability

- Nominal lifetime: 35,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 120 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 6500 K

Miscellaneous

- Especially designed for: Living Room
- EyeComfort: Yes

Product dimensions and weight

- Net weight: 0.08 kg
- Overall height: 10 mm
- Overall length: 80 mm
- Overall width: 80 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Diameter: 80 mm
- Total lumen output fixture: 190
- Light color: 6500
- Mains power: 220-240
- Fixture dimmable: No
- Wattage bulb included: 3
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated

Packaging dimensions and weight

- EAN/UPC – product: 8718696690826
- Net weight: 0.09 kg
- Gross weight: 0.29 kg
- Height: 4 cm
- Length: 10 cm
- Width: 8.6 cm



Issue date: 2025-08-30
Version: 0.378

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com