

# PHILIPS

Downlight

Functional

Astra Metallica

White

8718696722213



## Durable and bright

Philips premium Slim LED panel light with Aluminum housing for long life and bright light

### Match your interior

- Super slim design

### Light effect

- Bright light with uniform distribution
- Bright and even light

### Premium quality

- Durable and impact resistant die-cast aluminum housing
- EyeComfort - light that's easy on the eyes

### Material & finishing

- Durable aluminum housing

### Durability

- Long life span up to 25,000 hours

# Highlights

## Super slim design

Slim design is ideal for low-ceiling rooms, sitting flush against the surface.

## Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

## Bright and even light

Light is clear and distributed evenly around your space in a dependable manner.

## Durable and impact resistant die-cast aluminum housing

The die-cast aluminum housing of this item adds to a cultivated and refined contemporary atmosphere.

## Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

## Durable aluminum housing

Creates a strong, clean and contemporary style for your space.

## Long life span up to 25,000 hours

Philips LED technology extends your product's lifetime up to 25,000 hours

# Specifications

## Design and finishing

- Color: White
- Material: Metal

## Durability

- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 120
- Color rendering index (CRI): 80
- Color temperature: 3000 K

## Miscellaneous

- Especially designed for: Living Room
- EyeComfort: Yes

## Product dimensions and weight

- Net weight: 0.273 kg
- Overall height: 18 mm
- Overall length: 170 mm
- Overall width: 170 mm
- Recessed Ceiling cutout: 15.9 cm x 15.9 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Diameter: 170 mm
- Total lumen output fixture: 1500
- Bulb technology: LED
- Mains power: 220-240
- Fixture dimmable: No
- Wattage bulb included: 15
- IP code: IP20
- Class of protection: Class II - Double Insulated

### The bulb

- Software upgradable: No

### What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

### Packaging dimensions and weight

- EAN/UPC - product: 8718696722213
- Net weight: 0.25 kg
- Gross weight: 0.33 kg
- Height: 17.1 cm
- Length: 18.8 cm
- Width: 4.7 cm



Issue date: 2026-06-20  
Version: 0.442

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)