

PHILIPS

Recessed spot light

Functional

AstraSpot

White

8718696734988



Superior light and style

LED SpotLight designed for smaller spaces with sharp focus to create ambience

Match your interior

- Expressive and elegant form
- Add vibrancy to your room
- Compact design

Light effect

- Bright and focused beam

Highlights

Expressive and elegant form

A clean, modern design provides elegance and sophistication to your rooms.

Add vibrancy to your room

Introduce a splash of character and mark your personality into every room.

Compact design

Compact size allows luminaire to be placed in small spaces.

Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

Specifications

Design and finishing

- Color: White
- Material: Plastic

Durability

- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 30 degree(s)
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Living Room

Product dimensions and weight

- Net weight: 0.016 kg
- Overall height: 16 mm
- Overall length: 42 mm
- Overall width: 42 mm
- Recessed Ceiling cutout: 1.6 cm x 1.6 cm

Technical specifications

- Diameter: 42 mm
- Total lumen output fixture: 100
- Light color: Blue light
- Mains power: 220-240
- Fixture dimmable: No
- Wattage bulb included: 2
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated

Packaging dimensions and weight

- EAN/UPC – product: 8718696734988
- Net weight: 0.03 kg
- Gross weight: 0.04 kg
- Height: 4.5 cm
- Length: 4.5 cm
- Width: 4.5 cm



Issue date: 2025-11-01
Version: 0.74

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com