



Superior light and style

LED Tiltable COB Light designed for smaller spaces with sharp focus to create ambience

Designed for your living- and bedroom

· Create a stylish and welcoming atmosphere

Match your interior

- Compact size for small space
- · Add vibrancy to your room
- Compact design

Light effect

· Bright and focused beam

Material & finishing

· High quality metal material

Durability

· Long life span up to 15,000 hours

Highlights

Create a stylish atmosphere



This light is designed around the latest tastes, trends and lifestyles to blend effortlessly into your d?cor and define the localised ambiance you have always desired.

Compact size for small space

Perfect for fitting into small spaces

Add vibrancy to your room

Introduce a splash of character and mark your personality into every room.

Compact design

Compact size allows luminaire to be placed in small spaces.

Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

High quality metal material



Durable and attractive metal material for a strong finish.

Specifications

Design and finishing

Color: WhiteMaterial: Metal

Durability

• Nominal lifetime: 15,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- · Adjustable spot head: Yes
- · Dimmable with remote control: No
- LED integrated: Yes
- · Remote control included: No

Light characteristics

- Beam angle: 36 degree(s)
- · Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Living- & Bedroom
- · EyeComfort: No

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Product dimensions and weight

Net weight: 0.078 kgCut out length: 5.2 cmCut out width: 5.2 cmHeight: 4.5 cm

Height: 4.5 cmLength: 7.1 cmWidth: 7.1 cm

Service

Warranty: 2 year(s)

Technical specifications

• Diameter: 71 mm

· Total lumen output fixture: 240

Light color: 6500
Mains power: 220-240
Wattage bulb included: 3
IP code: IP20 | Finger-protected

• Class of protection: Class II - Double

Insulated

Packaging dimensions and weight [7W COB LED Deep Recessed CDL]

Net weight: 0.22 kgGross weight: 0.42 kg

Height: 0Length: 0Width: 0

Packaging dimensions and weight [3W Astra Spot TILT CDL]

• EAN/UPC - product: 8718696787069

Gross weight: 0.08 kgHeight: 5.5 cmLength: 8.2 cm

• Net weight: 0.08 kg

• Width: 8.2 cm



Issue date: 2025-11-05 Version: 0.127 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips