



Superior light and style

Decorative downlight made with high quality aluminium which blends well on your ceiling enhacning the décor.

Match your interior

· Decorative metallic finishing

Light effect

- Bright light with uniform distribution
- Durable synthetic diffuser for uniform light and reduced glare

Material & finishing

· Durable aluminum housing

Durability

• Long life span up to 30,000 hours

Highlights

Decorative metallic finishing

Contemporary metallic finishing adds a modern touch.

Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

Durable synthetic diffuser for uniform light and reduced glare

Provides a soft glow for relaxation and focus without distracting glare.

Durable aluminum housing

Creates a strong, clean and contemporary style for your space.

Long life span up to 30,000 hours

Philips LED technology extends your product's lifetime up to 30,000 hours.

Specifications

Bulb characteristics

Intended use: IndoorLamp shape: Round

Design and finishing

Color: WhiteMaterial: Metal

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- · Lumen maintenance factor: 70%
- Number of switch cycles: 10,000
- · Nominal lifetime: 15,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 120 degree(s)
- Color consistency: 5 SDCM
- · Color rendering index (CRI): 80
- · Color temperature: 4000 K
- · Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 90 lm/W

Miscellaneous

· Especially designed for: Living Room

Other characteristics

· Lamp current: 48 mA

Power consumption

Power factor: 0.5Voltage: 220-240 V

Product dimensions and weight

- · Net weight: 0.082 kg
- · Overall height: 45 mm
- · Overall length: 87 mm
- · Overall width: 87 mm
- Recessed Ceiling cutout: 7.8 cm x 7.8 cm

Service

· Warranty: 2 year(s)

Technical specifications

· Diameter: 87 mm

· Total lumen output fixture: 450

Light color: 4000
Mains power: 220-240
Fixture dimmable: No
Wattage bulb included: 5

IP code: IP20 | Finger-protectedClass of protection: Class II - Double

Insulated

Packaging dimensions and weight

• EAN/UPC - product: 8718699631437

Net weight: 0.08 kgGross weight: 0.12 kgHeight: 10.5 cmLength: 13.5 cm

• Width: 5 cm



Issue date: 2025-11-01 Version: 0.222 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips