



# Superior light and style

Philips Star Surface light fits perfectly in all your general spaces for a clean look. It is compact and easy to install and provides a soft uniformed glow through its quality synthetic diffuser

### Easy to experience

• Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

#### **Light effect**

- · Available in Warm White, Cool White or Cool Daylight
- Durable synthetic diffuser for uniform light and reduced glare

### **Safety**

· No harmful UV radiation

### **Premium quality**

• EyeComfort - light that's easy on the eyes

### **Durability**

· Long life span up to 15,000 hours

# Highlights

# Suitable for low ceilingsSlim design Available in Warm White, Cool White or Cool Daylight

Different light colors can affect mood: warm white is perfect for relaxation, cool white for concentration and cool daylight for energizing you

# Durable synthetic diffuser for uniform light and reduced glare

Provides a soft glow for relaxation and focus without distracting glare.

### No harmful UV radiation

The product is designed to eliminate any potentially harmful UV radiation.

#### **Evecomfort**

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they

meet EyeComfort requirements. Philip s LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

### Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

# Specifications

# Design and finishing

Color: WhiteMaterial: Plastic

### **Durability**

· Nominal lifetime: 15,000

### **Environmental**

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

### Extra feature/accessory incl.

- · Dimmable with remote control: No
- · LED integrated: Yes
- · Remote control included: No

### **Light characteristics**

• Beam angle: 120 degree(s)

Color rendering index (CRI): 80

· Color temperature: 4000 K

### Miscellaneous

· Especially designed for: Living Room

EyeComfort: Yes

# Product dimensions and weight

· Net weight: 0.535 kg

· Overall height: 25 mm

• Overall length: 300 mm

• Overall width: 300 mm

• Recessed Ceiling cutout: 0 cm x 0 cm

### Service

Warranty: 2 year(s)

### **Technical specifications**

· Diameter: 300 mm

Insulated

· Total lumen output fixture: 1650

Light color: 4000
Mains power: 220-240
Fixture dimmable: No
Wattage bulb included: 22
IP code: IP20 | Finger-protected
Class of protection: Class II - Double

### Packaging dimensions and weight

• EAN/UPC - product: 8718699687823

Net weight: 0.45 kgGross weight: 0.61 kg

Height: 31 cmLength: 31 cmWidth: 4 cm



Issue date: 2025-11-01 Version: 0.448 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips