

PHILIPS

Downlight

Functional

Full Glow Surface Light

White

8718699698850



Superior light and style

Premium rimless surface downlights with slim design which do not protrude much from the ceiling, provides wider and brighter light output. Ideal for places without false ceiling like balcony, kitchen patio, parking lots, rooms etc

Easy to experience

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

Light effect

- Bright light with uniform distribution
- Durable synthetic diffuser for uniform light and reduced glare

Durability

- Long life span up to 15,000 hours

Highlights

Suitable for low ceilings Slim design Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

Durable synthetic diffuser for uniform light and reduced glare

Provides a soft glow for relaxation and focus without distracting glare.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

Design and finishing

- Color: White
- Material: Plastic

Durability

- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 120 degree(s)
- Color consistency: 5 SDCM
- Color rendering index (CRI): 80
- Color temperature: 4000 K
- Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 100 lm/W

Miscellaneous

- Especially designed for: Living Room
- Style: Contemporary
- Type: Ceiling Lights

Other characteristics

- Lamp current: 34-53 mA

Power consumption

- Power factor: >0.5
- Voltage: 240 V

Product dimensions and weight

- Net weight: 0.075 kg
- Overall height: 29 mm
- Overall length: 102 mm
- Overall width: 102 mm
- Recessed Ceiling cutout: 0 cm x 0 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Diameter: 102 mm
- Total lumen output fixture: 600
- Light color: 4000
- Mains power: 220-240
- Fixture dimmable: No
- Wattage bulb included: 6
- IP code: IP20 | Finger-protected
- Class of protection: Class II - Double Insulated

Packaging dimensions and weight

- EAN/UPC - product: 8718699698850
- Net weight: 0.12 kg
- Gross weight: 0.16 kg
- Height: 11 cm
- Length: 11 cm
- Width: 3.2 cm



Issue date: 2025-09-03
Version: 0.74

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com