



Superior light and style

Premium rimless surface downlights with slim design which donot protrude much from the ceiling, provides wider and brighter light output. Ideal for places without false ceiling like balcony, kitchen patio, parking lots, rooms etc

Easy to experience

 Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

Light effect

- Bright light with uniform distribution
- ${\boldsymbol{\cdot}}$ Durable synthetic diffuser for uniform light and reduced glare

Durability

· Long life span up to 15,000 hours

Highlights

Suitable for low ceilingsSlim design Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

Durable synthetic diffuser for uniform light and reduced glare

Provides a soft glow for relaxation and focus without distracting glare.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Bulb characteristics

Intended use: IndoorLamp shape: Round

Design and finishing

Color: WhiteMaterial: Plastic

Durability

· Nominal lifetime: 15.000

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- · Remote control included: No

Light characteristics

- Beam angle: 120 degree(s)
- · Color consistency: 5 SDCM
- · Color rendering index (CRI): 80
- Color temperature: 3000 K
- Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 100 lm/W

Miscellaneous

· Especially designed for: Living Room

Style: ContemporaryType: Ceiling Lights

Other characteristics

· Lamp current: 95-132 mA

Power consumption

Power factor: >0.5Voltage: 240 V

Product dimensions and weight

Net weight: 0.25 kgOverall height: 29 mmOverall length: 200 mmOverall width: 200 mm

• Recessed Ceiling cutout: 0 cm x 0 cm

Service

Warranty: 2 year(s)

Technical specifications

· Diameter: 200 mm

· Total lumen output fixture: 1800

Light color: 3000Mains power: 220-240Fixture dimmable: NoWattage bulb included: 18

• IP code: IP20 | Finger-protected

 Class of protection: Class II - Double Insulated

Packaging dimensions and weight

• EAN/UPC - product: 8718699789794

Net weight: 0.3 kgGross weight: 0.37 kgHeight: 19 cm

Length: 19 cmWidth: 3.8 cm



Issue date: 2025-11-01 Version: 0.74 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N V