



High quality LED light designed to last for years

Surface mounted COB light to highlight the objects in the places where there is no false ceiling like corridors, shops etc.

Match your interior

· Decorative metallic finishing

Easy to experience

· Easy installation

Light effect

• Durable synthetic diffuser for uniform light and reduced glare

Premium quality

• Durable and impact resistant die-cast aluminum housing

Mounting

· Closed mounting for prevention of bugs and dirt ingress

Durability

· Long life span up to 30,000 hours

Highlights

Decorative metallic finishing

Contemporary metallic finishing adds a modern touch.

Easy installation

No more hassle in installation. Just fix or hang securely on the wall or ceiling, and plug in, now this luminaire is ready to light on.

Durable synthetic diffuser for uniform light and reduced glare

Provides a soft glow for relaxation and focus without distracting glare.

Durable and impact resistant die-cast aluminum housing

The die-cast aluminum housing of this item adds to a cultivated and refined contemporary atmosphere.

Closed mounting for prevention of bugs and dirt ingress

Prevents damage cause by bugs, dust or other foreign objects.

Long life span up to 30,000 hours

Philips LED technology extends your product's lifetime up to 30,000 hours.

Specifications

Design and finishing

Color: BlackMaterial: Metal

Durability

· Nominal lifetime: 35,000

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Dimmable with remote control: No
- · LED integrated: Yes
- · Remote control included: No

Light characteristics

Beam angle: 36 degree(s)Color rendering index (CRI): 80

Color temperature: 4000 K

Miscellaneous

· Especially designed for: Living Room

EyeComfort: No

Product dimensions and weight

Net weight: 0.609 kgOverall height: 140 mmOverall length: 90 mm

· Overall width: 90 mm

• Recessed Ceiling cutout: 0 cm x 0 cm

Service

Warranty: 2 year(s)

Technical specifications

• Diameter: 90 mm

Total lumen output fixture: 1530

Light color: 4000Mains power: 220-240Fixture dimmable: NoWattage bulb included: 18

• IP code: IP20 | Finger-protected

 Class of protection: Class II - Double Insulated

Packaging dimensions and weight

• EAN/UPC - product: 8719514260962

Gross weight: 0.75 kgHeight: 19 cmLength: 14 cm

· Net weight: 0.57 kg

· Width: 14 cm



Issue date: 2025-11-01 Version: 0.318 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips