



Comfortable light with a slimmer fit

Thin Trim COB has very minimalistic trim which blends well with the ceiling, This COB provides focussed 36 degree light beam to highlight the objects and the liht source is deep recessed so gives glare free light

Light effect

- Bright and focused beam
- $\boldsymbol{\cdot}$ Durable synthetic diffuser for uniform light and reduced glare

Premium quality

· Durable and impact resistant die-cast aluminum housing

Control

· Dimmable with wall switch

Durability

Long life span up to 30,000 hours

Highlights

Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

Durable synthetic diffuser for uniform light and reduced glare

Provides a soft glow for relaxation and focus without distracting glare.

Durable and impact resistant die-cast aluminum housing

The die-cast aluminum housing of this item adds to a cultivated and refined contemporary atmosphere.

Dimmable with wall switch

Lets you easily dim lights to the required level of brightness.

Long life span up to 30,000 hours

Philips LED technology extends your product's lifetime up to 30,000 hours.

Specifications

Design and finishing

Color: WhiteMaterial: Metal

Durability

· Nominal lifetime: 25.000

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- · Adjustable spot head: Not adjustable
- Dimmable with remote control: No
- · LED integrated: Yes
- · Remote control included: No

Light characteristics

Beam angle: 36 degree(s)Color rendering index (CRI): 80

· Color temperature: 3000 K

Miscellaneous

· Especially designed for: Living Room

· EyeComfort: No

Product dimensions and weight

· Net weight: 0.19 kg

• Overall height: 100 mm

• Overall length: 75 mm

• Overall width: 75 mm

• Recessed Ceiling cutout: 6.8 cm x 6.8

Service

• Warranty: 2 year(s)

Technical specifications

· Diameter: 75 mm

· Total lumen output fixture: 760

· Light color: 3000

• Mains power: 220-240

Fixture dimmable: No

• Wattage bulb included: 12

• IP code: IP20 | Finger-protected

 Class of protection: Class II - Double Insulated

Packaging dimensions and weight

• EAN/UPC - product: 8719514278141

Net weight: 0.21 kgGross weight: 0.24 kg

Height: 12.2 cmLength: 10.4 cm

• Width: 7.8 cm



Issue date: 2025-11-01 Version: 0.320

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips