



Comfortable light with a slimmer fit

Slim design surface light specially designed for smaller compact spaces like under cabinets

Designed for your living- and bedroom

· Create a stylish and welcoming atmosphere

Match your interior

Compact size for small space

Premium quality

• EyeComfort - light that's easy on the eyes

Durability

· Long life span up to 15,000 hours

Highlights

Create a stylish atmosphere



This light is designed around the latest tastes, trends and lifestyles to blend effortlessly into your d?cor and define the localised ambiance you have always desired.

Compact size for small space

Perfect for fitting into small spaces

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philip s LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality. output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Design and finishing

Color: WhiteMaterial: Plastic

Durability

• Nominal lifetime: 15,000

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- · Dimmable with remote control: No
- · LED integrated: Yes
- · Remote control included: No

Light characteristics

Beam angle: 120 degree(s)Color rendering index (CRI): 80

Miscellaneous

• Especially designed for: Living Room

Product dimensions and weight

Net weight: 0.03 kgOverall height: 12 mmOverall length: 65 mm

• Overall width: 65 mm

• Recessed Ceiling cutout: 0 cm x 0 cm

Technical specifications

Diameter: 65 mm

Total lumen output fixture: 150

Light color: Red lightMains power: 220-240Fixture dimmable: No

• Wattage bulb included: 3

• IP code: IP20 | Finger-protected

 Class of protection: Class II - Double Insulated

Packaging dimensions and weight

• EAN/UPC - product: 8719514294349

Net weight: 0.03 kgGross weight: 0.04 kg

Height: 7.2 cmLength: 7.2 cmWidth: 2 cm



Issue date: 2025-11-01 Version: 0.74 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips