

Filament Bulb amber 7W (Eq.50W) A60 E27

Smart LED

Tunable white

Glass

Easy plug and play

Control with WiZ app or voice



8719514372023



Choose from warm or cool white light

Get smart light with a vintage look with the Philips Smart LED Filament bulb with an E27 base, which offers an amber coating with warm or cool white light. This bulb is WiZ connected. Use with your existing Wi-Fi to control with the WiZ app or your voice.

Easy setup

• Easy plug and play. Works with your existing Wi-Fi.

Smart control

- · Control anywhere with your smartphone.
- · Voice control with Google Assistant, Alexa or Siri Shortcuts

Smart features

- · Smart dimming via app, voice or dimmer
- · Automate your light with schedules
- Energy monitoring

Light modes

- Tunable warm to cool white and preset modes
- Customize Scenes with preset dynamic light modes.

Highlights

Easy plug and play

WiZ works with your existing Wi-Fi router, no additional gateway is needed. Simply plug in your new light, download the WiZ app and you're ready to go!

Control from anywhere

Control your WiZ lights wherever you are with smartphone. No need to worry if you've left your lights on before leaving home. WiZ app is available for iOS and Android.

Voice Control

Get hands-free control of your lights by using your voice and Google Assistant, Amazon Alexa or Siri Shortcuts. Use simple voice commands to turn lights on or off, brighten and dim, change color, and set custom light Scenes.

Smart dimming

Dim your lights to your desired brightness level via your smartphone, the WiZmote or your voice. No need to install an expensive dimmer.

Automate your light with schedules

Automate the lights to fit your daily or weekly routines. Schedule your light to turn on before you arrive home and keep it off when not needed.

Energy monitoring

The WiZ app keeps records of the energy consumption of your lights. View your weekly or daily report and plan your lighting wisely for an optimized energy consumption at home.

Tunable warm to cool white and preset modes

Choose from a wide range of energizing cool white to soft warm white, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.

Customized Scenes

Mix different color and white lights modes to create the perfect light ambience for your daily moment. Save it and call it out anytime with app, WiZmote or voice.

Specifications

Bulb characteristics

Intended use: IndoorLamp shape: A60Socket: E27

Type of glass: AmberBulb Finish: AmberDimmable: Yes

Bulb dimensions

· Weight: 0.042 kg

Durability

Average life (at 2.7 hrs/day): 15 year(s)

Lumen maintenance factor: 70%Number of switch cycles: 20,000

· Nominal lifetime: 15,000

Light characteristics

- · Color consistency: 6 SDCM
- . Color rendering index (CRI): ≥90
- · Color temperature: 2000-5000 K
- · Light Color Category: Tunable white
- Nominal luminous flux: 640 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: instant full light
- Luminous Efficacy (rated) (Nom): 91 lm/W

Miscellaneous

EyeComfort: Yes

Other characteristics

· Lamp current: 43 mA

Packaging information

• EAN: 8719514372023

• EOC: 871951437202300

 Product title: PHI WFB 50W A60 E27 920-50 Amb 1PF/6

Power consumption

Power factor: 0.5Voltage: 220-240 V

Wattage equivalent: 50 WEnergy Efficiency Class: FPower Consumption: 7 W

• Energy Consumption kWh/1000 h: 7

Product dimensions and weight

Overall height: 106 mmOverall length: 106 mmOverall width: 60 mm

Rated values

Rated lifetime: 15,000Rated luminous flux: 640 lm

· Rated power: 7 W

Service

Warranty: 2 year(s)

Technical specifications

• Frequency: 50-60

• EPREL Registration Number: 1901124

What's supported

· Compatible with Effects: Yes

· WiFi: Wireless G

Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999

 Communication protocol: Bluetooth, WiFi (2.4GHz)

VVII 1 (2. 10112)

Packaging dimensions and weight

• EAN/UPC - product: 8719514372023

Net weight: 0.04 kgGross weight: 0.09 kg

Height: 16 cmLength: 7 cmWidth: 7 cm



Issue date: 2025-11-19 Version: 0.232 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips