

Filament Candle amber 4.9W (Eq.25W) C35 E14

**Smart LED** 

Tunable white

Glass

Easy plug and play

Control with WiZ app or voice



8719514372085



# Choose from warm or cool white light

Add smart light to your smaller lamps with the amber glow of a Philips Smart LED tunable white vintage-style Filament candle bulb with an E14 base. This bulb is WiZ connected. Use with your existing Wi-Fi to control with the WiZ app or your voice.

#### Easy setup

• Easy plug and play. Works with your existing Wi-Fi.

#### **Smart control**

- · Control anywhere with your smartphone.
- · Voice control with Google Assistant, Alexa or Siri Shortcuts

# **Smart features**

- · Smart dimming via app, voice or dimmer
- Automate your light with schedules
- Energy monitoring

### **Light modes**

- Tunable warm to cool white and preset modes
- · Customize Scenes with preset dynamic light modes.

# Highlights

# Easy plug and play

WiZ works with your existing Wi-Fi router, no additional gateway is needed. Simply plug in your new light, download the WiZ app and you're ready to go!

#### Control from anywhere

Control your WiZ lights wherever you are with smartphone. No need to worry if you've left your lights on before leaving home. WiZ app is available for iOS and Android.

#### **Voice Control**

Get hands-free control of your lights by using your voice and Google Assistant, Amazon Alexa or Siri Shortcuts. Use simple voice commands to turn lights on or off, brighten and dim, change color, and set custom light Scenes.

# **Smart dimming**

Dim your lights to your desired brightness level via your smartphone, the WiZmote or your voice. No need to install an expensive dimmer.

#### Automate your light with schedules

Automate the lights to fit your daily or weekly routines. Schedule your light to turn on before you arrive home and keep it off when not needed.

#### **Energy monitoring**

The WiZ app keeps records of the energy consumption of your lights. View your weekly or daily report and plan your lighting wisely for an optimized energy consumption at home.

# Tunable warm to cool white and preset modes

Choose from a wide range of energizing cool white to soft warm white, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.

#### **Customized Scenes**

Mix different color and white lights modes to create the perfect light ambience for your daily moment. Save it and call it out anytime with app, WiZmote or voice.

# Specifications

### **Bulb characteristics**

Intended use: IndoorLamp shape: C35Socket: E14

Type of glass: AmberBulb Finish: AmberDimmable: Yes

#### **Bulb dimensions**

· Weight: 0.03 kg

#### **Durability**

Average life (at 2.7 hrs/day): 15 year(s)

Lumen maintenance factor: 70%Number of switch cycles: 20,000

· Nominal lifetime: 15,000

#### **Light characteristics**

- · Color consistency: 6 SDCM
- · Color rendering index (CRI): ≥90
- · Color temperature: 2000-5000 K
- · Light Color Category: Tunable white
- · Nominal luminous flux: 370 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: instant full light
- Luminous Efficacy (rated) (Nom): 75 lm/W

# Miscellaneous

• EyeComfort: Yes

#### Other characteristics

· Lamp current: 33 mA

# **Packaging information**

- EAN: 8719514372085
- EOC: 871951437208500
- Product title: PHI WFB 25W C35 E14 920-50 Amb 1PF/6

# **Power consumption**

Power factor: 0.5Voltage: 220-240 V

Wattage equivalent: 25 W
Energy Efficiency Class: G
Power Consumption: 4.9 W

• Energy Consumption kWh/1000 h: 5

#### Product dimensions and weight

Overall height: 113 mmOverall length: 113 mmOverall width: 35 mm

#### **Rated values**

Rated lifetime: 15,000Rated luminous flux: 370 lmRated power: 4.9 W

#### Service

Warranty: 2 year(s)

# **Technical specifications**

• Frequency: 50-60

• EPREL Registration Number: 1901129

#### What's supported

· Compatible with Effects: Yes

· WiFi: Wireless G

Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999

 Communication protocol: Bluetooth, WiFi (2.4GHz)

#### Packaging dimensions and weight

• EAN/UPC - product: 8719514372085

Net weight: 0.03 kgGross weight: 0.07 kg

Height: 16 cmLength: 7 cmWidth: 7 cm



Issue date: 2025-11-19 Version: 0.199 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips