



# High quality LED light designed to last for years

Surface mounted COB light in decorative finishes to highlight the objects in the places where there is no false ceiling like corridors, shops etc.

#### Match your interior

· Decorative metallic finishing

## **Light effect**

• Durable synthetic diffuser for uniform light and reduced glare

# **Premium quality**

· Durable and impact resistant die-cast aluminum housing

#### Mounting

· Closed mounting for prevention of bugs and dirt ingress

# Highlights

#### Decorative metallic finishing

Contemporary metallic finishing adds a modern touch.

# Durable synthetic diffuser for uniform light and reduced glare

Provides a soft glow for relaxation and focus without distracting glare.

# Durable and impact resistant die-cast aluminum housing

The die-cast aluminum housing of this item adds to a cultivated and refined contemporary atmosphere.

# Closed mounting for prevention of bugs and dirt ingress

Prevents damage cause by bugs, dust or other foreign objects.

# Specifications

#### **Bulb characteristics**

Intended use: IndoorLamp shape: Round

## Design and finishing

Color: BlackMaterial: Metal

## **Durability**

Lumen maintenance factor: 70%
Nominal lifetime: 35 000

#### **Environmental**

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

#### Extra feature/accessory incl.

· Dimmable with remote control: No

LED integrated: Yes

· Remote control included: No

## **Light characteristics**

Beam angle: 36 degree(s)Color consistency: 5 SDCM

· Color rendering index (CRI): 80

· Color temperature: 3000 K

· Warm-up time to 60% light: 2

 Luminous Efficacy (rated) (Nom): 75 lm/W

#### Miscellaneous

· Especially designed for: Living Room

#### Other characteristics

· Lamp current: 170 mA

#### **Power consumption**

· Voltage: 220-240 V

#### Product dimensions and weight

• Net weight: 0.17 kg

• Overall height: 73 mm

· Overall length: 56 mm

· Overall width: 56 mm

• Recessed Ceiling cutout: 0 cm x 0 cm

## Service

· Warranty: 2 year(s)

## **Technical specifications**

Diameter: 56 mm

· Total lumen output fixture: 525

· Light color: 3000

• Mains power: 220-240

Fixture dimmable: No

· Wattage bulb included: 7

• IP code: IP20 | Finger-protected

 Class of protection: Class II - Double Insulated

## Packaging dimensions and weight

• EAN/UPC - product: 8719514418257

· Net weight: 0.17 kg

· Gross weight: 0.19 kg

· Height: 8.5 cm

· Length: 6.2 cm

· Width: 6.2 cm



Issue date: 2025-11-01 Version: 0.74 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.