



# Superior light and style

Premium rimless surface downlights with slim design which donot protrude much from the ceiling, provides wider and brighter light output. Ideal for places without false ceiling like balcony, kitchen patio, parking lots, rooms etc

#### Easy to experience

 Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

### **Light effect**

- Bright light with uniform distribution
- ${\boldsymbol{\cdot}}$  Durable synthetic diffuser for uniform light and reduced glare

#### **Durability**

· Long life span up to 15,000 hours

# Highlights

### Suitable for low ceilingsSlim design Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

## Durable synthetic diffuser for uniform light and reduced glare

Provides a soft glow for relaxation and focus without distracting glare.

#### Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

# Specifications

#### Design and finishing

Color: WhiteMaterial: Plastic

#### **Durability**

· Nominal lifetime: 15,000

#### **Environmental**

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

#### Extra feature/accessory incl.

· Dimmable with remote control: No

· LED integrated: Yes

· Remote control included: No

### **Light characteristics**

Beam angle: 120 degree(s)Color rendering index (CRI): 80Color temperature: 3000 K

#### Miscellaneous

· Especially designed for: Living Room

#### Product dimensions and weight

Net weight: 0.245 kgOverall height: 29 mmOverall length: 200 mmOverall width: 200 mm

• Recessed Ceiling cutout: 0 cm x 0 cm

#### **Technical specifications**

· Diameter: 200 mm

Total lumen output fixture: 2400

Light color: 3000
Mains power: 220-240
Fixture dimmable: No
Wattage bulb included: 24
IP code: IP20 | Finger-protected

 Class of protection: Class II - Double Insulated

#### Packaging dimensions and weight

• EAN/UPC - product: 8719514473478

Net weight: 0.3 kgGross weight: 0.37 kgHeight: 19 cmLength: 19 cm

Length: 19 cmWidth: 3.8 cm



Issue date: 2025-11-01 Version: 0.74

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips