



Durable and bright

Philips premium LED downlights with deep recessed diffusor to help reduce the glare along with thin trim design to blend well with the ceiling

Match your interior

· Super slim design

Light effect

• Bright light with uniform distribution

Premium quality

• EyeComfort - light that's easy on the eyes

Highlights

Super slim design

Slim design is ideal for low-ceiling rooms, sitting flush against the surface.

Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they

meet EyeComfort requirements. Philip s LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Specifications

Design and finishing

Color: WhiteMaterial: Plastic

Durability

· Nominal lifetime: 15,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- · Remote control included: No

Light characteristics

Beam angle: 120 degree(s)Color rendering index (CRI): 80

· Color temperature: 4000 K

Miscellaneous

Especially designed for: Living Room

Product dimensions and weight

Net weight: 0.14 kg
Overall height: 26 mm
Overall length: 167 mm
Overall width: 167 mm

Recessed Ceiling cutout: 15.24 cm x
 15.24 cm

Technical specifications

· Diameter: 167 mm

Total lumen output fixture: 1500

Light color: 4000
Mains power: 220-240
Fixture dimmable: No
Wattage bulb included: 15
IP code: IP20 | Finger-protected
Class of protection: Class II - Double Insulated

Packaging dimensions and weight

• EAN/UPC - product: 8719514478350

Net weight: 0.14 kgGross weight: 0.19 kgHeight: 4.5 cmLength: 18.5 cm

• Width: 17.5 cm



Issue date: 2025-11-01 Version: 0.74 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips