

PHILIPS

Profile Shine

240 Led strip

240 LEDs/m ensuring no dark spots

Uniform brightness with 900 lumens/meter

8720169161672



Eyecomfort

The Philips Profile Shine LED Strip Light offers professional-grade illumination for profile lighting and home décor accents. With 240 bright, energy-efficient LEDs over a 5-metre length, it delivers uniform brightness and dynamic color options — Warm White, Natural White, and Cool Daylight. Crafted from durable polycarbonate, it ensures long-lasting performance, while the adhesive-backed design allows for easy and flexible installation. Perfect for highlighting architectural details or adding a modern glow to any space.

Limitless possibilities

- Lengthen your strip lighting
- Weatherproof light strip
- Flexible light strip to shape and bend

Safety and Robust

- Silver contact and multilayer copper strips

Form factor

- Bendable outdoor linear strip light

Highlights

Lengthen your strip lighting



Extend your Philips Hue Lightstrip Plus up to 33 feet by adding 40 inch extensions to cover larger surfaces and enable wider applications.

Weatherproof light strip



The outdoor light strip can withstand all weather conditions, from small puddles of water to a downpour that lasts for hours.

Flexible light strip



Completely flexible, the outdoor light strip lets you shape, bend, and manipulate it to shine its light the way you want. Line a winding outdoor path or let it meander up a wall or column; with the included clips and screws, you can install it anywhere.

Silver contact and multilayer copper strips

Robust design with high quality silver contact, multilayer copper strips.

Bendable strip with linear light



Our silicone-based outdoor light strip is flexible. Bend it to outline the borders of your garden, to highlight the edges of your balcony, or into shape that you desire. Linear and uniform light effects with no visible LED dots are perfect for decorating all of your outdoor spaces.

Specifications

Bulb characteristics

- Dimmable: No

Design and finishing

- Color: White
- Material: Polycarbonate

Durability

- Nominal lifetime: 700,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: No
- Choose your color: No
- LED integrated: Yes
- On/off switch on wire: Yes
- Power adapter included: Yes

Light characteristics

- Color rendering index (CRI): -
- Luminous Efficacy (rated) (Nom): 900

String light/Lightstrip

- Extendibility: No

Miscellaneous

- Especially designed for: Balcony, Outside, Garden, Staircase
- Style: Not Applicable
- EyeComfort: Yes

Power consumption

- Energy Consumption kWh/1000 h: 1

Product dimensions and weight

- Net weight: 0.075 kg
- Overall height: 109 mm
- Overall length: 19 mm
- Overall width: 109 mm

Service

- Warranty: 1 year(s)

Technical specifications

- Total lumen output fixture: 4500
- Bulb technology: LED
- Light color: Neutral white light
- Mains power: 12 V
- IP code: IP65
- Class of protection: NA
- Light source replaceable: Yes
- Number of light sources: 240
- UL Wet/ damp/ dry location: Dry location
- Mounting options: Ceiling, TV, Wall, Window

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8721103122155
- Net weight: 0.08 kg
- Gross weight: 0.1 kg
- Height: 1.9 cm
- Length: 10.9 cm
- Width: 10.9 cm



Issue date: 2026-06-13
Version: 0.28

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com