

PHILIPS

Downlight

Functional

UltraGlow 3 in1

White

8720169174689



Set your desired ambiance at your fingertips

Change your room ambiance to suit whatever you're doing. With the Philips SceneSwitch LED downlight, you can easily change the setting from bright light, to natural light and to a cozy warm glow. Comfortable light that's easy on your eyes. No dimmer or additional installation required. All you need is your existing switch.

Easy to experience

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.
- Enhance your momentTunable with memory function

Light effect

- SceneSwitch color change

Premium quality

- EyeComfort - light that's easy on the eyes

Highlights

Suitable for low ceilings Slim design Enhance your moment Tunable with memory function

Memorize your favorite tunings of different light settings to easily find your perfect level of illumination.

SceneSwitch color change

SceneSwitch Color Change lets you set the overall mood of a living space at home. Stay focused with cool daylight, be more productive with cool white light or wind down and relax with warm white light. In essence, consumers can control the lights in their home according to their daily activities.

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Specifications

Design and finishing

- Color: White
- Material: Plastic

Durability

- Nominal lifetime: 25,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 120 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000-6500 K

Miscellaneous

- Especially designed for: Living Room

Product dimensions and weight

- Net weight: 0.095 kg
- Overall height: 21 mm
- Overall length: 130 mm
- Overall width: 130 mm

Technical specifications

- Diameter: 130 mm
- Total lumen output fixture: 1000
- Light color: 3000-6500
- Mains power: 220-240
- Fixture dimmable: No
- Wattage bulb included: 10
- IP code: IP20 | Finger-protected
- Class of protection: Class II - Double Insulated

Packaging dimensions and weight

- EAN/UPC - product: 8720169174689
- Net weight: 0.1 kg
- Gross weight: 0.15 kg
- Height: 14.2 cm
- Length: 14.8 cm
- Width: 4.8 cm



Issue date: 2025-08-30
Version: 0.74

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com