



# Superior light and style

LED COB Light designed for smaller spaces with sharp focus to create ambience

## Match your interior

- Compact size for small space
- · Add vibrancy to your room
- Compact design

# **Premium quality**

• Durable and impact resistant die-cast aluminum housing

# Highlights

#### Compact size for small space

Perfect for fitting into small spaces

#### Add vibrancy to your room

Introduce a splash of character and mark your personality into every room.

#### Compact design

Compact size allows luminaire to be placed in small spaces.

# Durable and impact resistant die-cast aluminum housing

The die-cast aluminum housing of this item adds to a cultivated and refined contemporary atmosphere.

# Specifications

#### Design and finishing

Color: WhiteMaterial: Metal

# **Durability**

· Nominal lifetime: 15,000

### **Environmental**

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

#### Extra feature/accessory incl.

· Dimmable with remote control: No

· LED integrated: Yes

· Remote control included: No

# **Light characteristics**

Beam angle: 30 degree(s)Color rendering index (CRI): 80Color temperature: 3000 K

### Miscellaneous

· Especially designed for: Living Room

#### Product dimensions and weight

Net weight: 0 kgOverall height: 23 mmOverall length: 32 mm

• Overall width: 32 mm

• Recessed Ceiling cutout: 2.7 cm x 2.7

#### **Technical specifications**

· Diameter: 32 mm

· Total lumen output fixture: 60

Light color: 3000Mains power: 220-240Fixture dimmable: NoWattage bulb included: 1

IP code: IP20 | Finger-protected
Class of protection: Class II - Double Insulated

### Packaging dimensions and weight

• EAN/UPC - product: 8720169223592

Net weight: 0.03 kgGross weight: 0.03 kg

Height: 5.7 cmLength: 5.7 cmWidth: 5.7 cm



Issue date: 2025-11-01 Version: 0.74 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.