



# Superior light and style

Premium COB Light with metal heat sink to create perfect ambience in the room

### Designed for your living- and bedroom

· Create a stylish and welcoming atmosphere

### Match your interior

· Add vibrancy to your room

### **Light effect**

· Bright and focused beam

# Material & finishing

· High quality metal material

# Highlights

### Create a stylish atmosphere



This light is designed around the latest tastes, trends and lifestyles to blend effortlessly into your d?cor and define the localised ambiance you have always desired.

# Add vibrancy to your room

Introduce a splash of character and mark your personality into every room.

### Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

### High quality metal material



Durable and attractive metal material for a strong finish.

# Specifications

#### Design and finishing

Color: WhiteMaterial: Metal

### **Durability**

· Nominal lifetime: 15,000

# Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

### Extra feature/accessory incl.

- Adjustable spot head: Adjustable rise and fall
- · Dimmable with remote control: No
- · LED integrated: Yes
- · Remote control included: No

### **Light characteristics**

Beam angle: 30 degree(s)Color rendering index (CRI): 80

· Color temperature: 6500 K

#### Miscellaneous

· Especially designed for: Living Room

# Product dimensions and weight

· Net weight: 0 kg

· Overall height: 80 mm

· Overall length: 120 mm

· Overall width: 120 mm

 Recessed Ceiling cutout: 80.0 cm x 80.0 cm

### **Technical specifications**

· Diameter: 120 mm

• Total lumen output fixture: 1500

Light color: 6500

• Mains power: 220-240

· Fixture dimmable: No

· Wattage bulb included: 20

• IP code: IP20 | Finger-protected

· Class of protection: Class II - Double

Insulated

# Packaging dimensions and weight

• EAN/UPC - product: 8720169240032

Net weight: 0.51 kg

· Gross weight: 0.57 kg

• Height: 92 cm

· Length: 132 cm

· Width: 132 cm



Issue date: 2025-11-01 Version: 0.74 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips