



Bi-directional beam

Superior illumination. Classic anthracite finish. Premium aluminium material. Optimum performance

Light effect

· Provides a bright white light

Sustainable light solutions

· High quality LED light

Beacon of trust

· You can trust what the Philips packaging is saying

Premium quality

• Die-casted aluminum for a premium look and feel

Specially designed for your outdoors

• Resistant to all weather conditions

Highlights

Superior light quality High quality LED light



The LED technology, integrated into this Philips lamp, is a uniquely developed solution by Philips. While instantly turned on, it enables an optimal light output and brings out vivid colors in your home.

Reliable quality

Philips keeps its promises about lamp performance. You can trust what the Philips packaging is saying about light output, lifetime and wattage equivalent to incandescent lamps.

Premium materials



Resistant to all weather



This Philips Hue outdoor sensor is specially designed for use in outdoor environments and has undergone rigorous tests to ensure its performance. This lamp is designed with IP54: it is protected against water splashed from any direction. The product will withstand heavy rainfall and other weather conditions.

Specifications

Bulb characteristics

· Intended use: Outdoor

Design and finishing

· Color: Grey

· Material: Aluminium

Durability

· Nominal lifetime: 25,000

Extra feature/accessory incl.

· Anti rust anti dust: Yes

· Bi-directional light beams: Yes

· Centerpiece: Yes

• Fully weatherproof: Yes

· LED integrated: Yes

• Made for LED only: Yes

 Perfectly suited for up/down mounting: Yes

· Photometric data available: Yes

· Premium quality material: Yes

• Resistant high quality material: Yes

· Warm White Light: Yes

· Waterproof: Yes

Light characteristics

· Color rendering index (CRI): 80

Miscellaneous

 \bullet Especially designed for: Garden &

Patio

Style: ExpressiveType: Spot Light

Service

· Warranty: 1 year(s)

Technical specifications

• Total lumen output fixture: 382

Bulb technology: LEDLight color: 3000K

• Mains power: 220-240 V

Wattage bulb included: 7

• IP code: IP44 | Wire-protected and

splash-proofClass of protection: Class I - Earthed

Packaging dimensions and weight

• EAN/UPC - product: 8727900078237

Net weight: 0.59 kgGross weight: 0.69 kg

· Height: 5.5 cm

• Length: 17.5 cm

• Width: 8.5 cm



Issue date: 2025-11-01 Version: 0.434 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips