



Classical Indian appeal

Beautiful light pattern. Matt gold for superior finish

Beacon of trust

You can trust what the Philips packaging is saying

Premium quality

• Die-casted aluminum for a premium look and feel

Highlights

Reliable quality

Philips keeps its promises about lamp performance. You can trust what the Philips packaging is saying about light output, lifetime and wattage equivalent to incandescent lamps.

Premium materials



Specifications

Bulb characteristics

· Intended use: Indoor

Design and finishing

· Color: Gold

· Material: Aluminium

Extra feature/accessory incl.

· LED integrated: No

· Premium quality material: Yes

Miscellaneous

Especially designed for: Home office
 Study

Style: ModernType: Floor Lamp

Service

• Warranty: 1 year(s)

Technical specifications

• Mains power: 220-240 V

Energy class included light source: no bulb included

ID ---I- ID20 | Fire--

IP code: IP20 | Finger-protected
Class of protection: Class II - Double
Insulated

 $. \ Light source \ replaceable: Yes$

· Number of light sources: 1

Packaging dimensions and weight

• EAN/UPC - product: 8718291656074

Net weight: 4.25 kgGross weight: 0.58 kgHeight: 28 cm

Length: 45.8 cmWidth: 16.5 cm



Issue date: 2025-11-22 Version: 0.459 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips