



Light and Relaxed

Expressive & elegant form. Beautiful light pattern. Classical Indian appeal

Beacon of trust

· You can trust what the Philips packaging is saying

Premium quality

• Durable metallic housing

Indulge your sense of style

Frosted glass

Material & finishing

• Easy to clean glass

Highlights

Reliable quality

Philips keeps its promises about lamp performance. You can trust what the Philips packaging is saying about light output, lifetime and wattage equivalent to incandescent lamps.

Durable metallic housing Frosted glass

Frosted glass combines a matt white look with the elegance of glass material, blending perfectly in any interior.

Easy to clean glass

Means your products remain attractive for years to come.

Specifications

Bulb characteristics

Intended use: Indoor

Design and finishing

Color: BlackMaterial: Metal

Extra feature/accessory incl.

Adjustable height: YesLED integrated: No

· Premium quality material: Yes

Miscellaneous

 Especially designed for: Living- & Bedroom

Style: ModernType: Ceiling Lights

Service

Warranty: 1 year(s)

Technical specifications

• Mains power: 220-240 V

Energy class included light source: no bulb included

Wattage bulb included: 23
IP code: IP20 | Finger-protected
Class of protection: Class I - Earthed

Light source replaceable: YesNumber of light sources: 1

Packaging dimensions and weight

• EAN/UPC - product: 8718696722558

Net weight: 1.23 kg
Gross weight: 1.35 kg
Height: 12.2 cm
Length: 30 cm
Width: 12.2 cm



Issue date: 2025-11-01 Version: 0.441 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.