

PHILIPS

Wall light

Led outdoor

2 Watt

Aluminium

Grey

IP 44

919215850650



IP 44 fixtures ideal for gardens

Grey powder coated aluminium fixture. Sleek design. Warm white light

Ease of use

- Moisture resistant

Light effect

- Provides a bright white light

Sustainable light solutions

- High quality LED light

Beacon of trust

- You can trust what the Philips packaging is saying

Premium quality

- Die-casted aluminum for a premium look and feel

Highlights

Moisture resistant
Superior light quality
High quality LED light



The LED technology, integrated into this Philips lamp, is a uniquely developed solution by Philips. While instantly turned on, it enables an optimal light output and brings out vivid colors in your home.

Reliable quality

Philips keeps its promises about lamp performance. You can trust what the Philips packaging is saying about light output, lifetime and wattage equivalent to incandescent lamps.

Premium materials



Specifications

Bulb characteristics

- Intended use: Outdoor

Design and finishing

- Color: Grey
- Material: Aluminium

Durability

- Nominal lifetime: 25,000

Extra feature/accessory incl.

- Anti rust anti dust: Yes
- Centerpiece: Yes
- Diffused light effect: Yes
- LED integrated: Yes
- Made for LED only: Yes
- Photometric data available: Yes
- Premium quality material: Yes
- Resistant high quality material: Yes
- Warm White Light: Yes
- Waterproof: Yes

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Garden & Patio
- Style: Modern
- Type: Wall Lights
- EyeComfort: Yes

Service

- Warranty: 1 year(s)

Technical specifications

- Bulb technology: LED
- Light color: 3000K
- Mains power: 220-240 V
- Wattage bulb included: 2
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class II - Double Insulated

Packaging dimensions and weight

- EAN/UPC - product: 8718696697597
- Net weight: 0.15 kg
- Gross weight: 0.17 kg
- Height: 4.4 cm
- Length: 8.4 cm
- Width: 8.4 cm



Issue date: 2025-08-30
Version: 0.437

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com