

PHILIPS

Wall light

myLiving

2 x GU10

Metal

Chrome

220-240 V

919215850819



Modern design to compliment home décor

Premium pressed clear glass for sparkling light. Premium aesthetic elegant chrome finish

Easy installation

- Easy installation

Beacon of trust

- You can trust what the Philips packaging is saying

Premium quality

- Durable metallic housing

Highlights

Easy installation



No more hassle in installation. Just fix or hang securely on the wall and plug in, now this luminaire is ready to light on.

Reliable quality

Philips keeps its promises about lamp performance. You can trust what the Philips packaging is saying about light output, lifetime and wattage equivalent to incandescent lamps.

Durable metallic housing

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: Chrome
- Material: Metal

Extra feature/accessory incl.

- Premium quality material: Yes

Miscellaneous

- Especially designed for: Home office & Study
- Style: Modern
- Type: Wall Lights

Service

- Warranty: 1 year(s)

Technical specifications

- Mains power: 220–240 V
- Energy class included light source: no bulb included
- Number of bulbs: 2
- IP code: IP20 | Finger-protected
- Class of protection: Class I – Earthed
- Light source replaceable: Yes
- Number of light sources: 2

Packaging dimensions and weight

- EAN/UPC – product: 8719514256842
- Net weight: 1.65 kg
- Gross weight: 2.35 kg
- Height: 22 cm
- Length: 42 cm
- Width: 16 cm



Issue date: 2025-08-30
Version: 0.437

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com