

# PHILIPS

IP65 dust-proof and  
water-resistant garden  
spike

myGarden

Robust built and durable  
quality;

Dust-proof and water resistant;

Perfect for use in garden, patio;

36 degree beam angle to  
ensure spread of light

919215851088



## Bring your outdoors alive!

This well-designed modern and rugged garden spike is a great way to highlight your garden spaces. COB integrated lighting keeps the product high on light dispersion and efficiency

**Bring design into your garden**

- Decorative outdoor lighting

# Highlights

## Decorative outdoor lighting

Outdoor lighting can improve the look of your garden or outside space, illuminating eye-catching features,

lighting pathways with style or creating the perfect ambience for those memorable evenings with friends and family. This Philips outdoor light

provides beautiful decorative outdoor lighting with the flair and functionality to help you make the most of your outdoor space in your own style.

# Specifications

## Bulb characteristics

- Intended use: Outdoor

## Bulb dimensions

- Height: 7.5 cm

## Design and finishing

- Color: Anthracite Grey
- Material: Aluminium

## Extra feature/accessory incl.

- 4 light recipes: No
- 5 years warranty on the LED module: No
- Adjustable height: No
- Adjustable spot head: Yes
- Batteries included: No
- Bi-directional light beams: No
- Candle light effect: No
- Centerpiece: No
- Choose your color: No
- Clamp included: Yes
- Color changing (LED): No
- Day-and-night sensor: No
- Defined light beams: No
- Fully weatherproof: Yes
- Hue bridge included: No
- Hue Switch: No
- Hue Switch Included: No
- LED integrated: Yes
- Premium quality material: Yes

## Light characteristics

- Beam angle: 36 degree(s)
- Color rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Garden & Patio

## Product dimensions and weight

- Net weight: 0.283 kg
- Height: 7.5 cm
- Length: 7.5 cm
- Width: 7.5 cm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Lamp lifetime up to: 20,000
- Total lumen output fixture: 10
- Bulb technology: LED
- Light color: Red
- Mains power: 220-240 V
- Energy class included light source: built in LED + bulb of class A+
- IP code: IP65 | Dust-tight and jet-proof

## Packaging dimensions and weight

- EAN/UPC – product: 8719514498594
- Net weight: 0.28 kg
- Gross weight: 0.32 kg
- Height: 6.5 cm
- Length: 16.5 cm
- Width: 7.6 cm



Issue date: 2025-08-30  
Version: 0.117

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)