

919215851201



Designed elegantly for superior lighting

Ignite the charm of your surroundings with modern and elegantly designed wall light. Now relax, focus, and celebrate every moment with the right light.

Light modes

· Tunable warm to cool white and preset modes

Highlights

Tunable warm to cool white and preset modes

Choose from a wide range of energizing cool white to soft warm

white, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.

Specifications

Bulb characteristics

· Intended use: Indoor

Bulb dimensions

· Height: 17 cm

Design and finishing

Color: ChromeMaterial: Metal

Durability

· Nominal lifetime: 20.000

Extra feature/accessory incl.

- · 4 light recipes: No
- 5 years warranty on the LED module:
- · Adjustable height: No
- · Adjustable spot head: No
- · Batteries included: No
- · Bi-directional light beams: No
- · Candle light effect: No
- · Centerpiece: No
- · Choose your color: No
- · Clamp included: Yes
- Color changing (LED): Yes
- · Day-and-night sensor: No
- Defined light beams: No
- Fully weatherproof: No
- · Hue bridge included: No
- · Hue Switch: No
- · Hue Switch Included: No
- LED integrated: Yes
- Perfectly suited for ambiance creation: Yes
- · Premium quality material: Yes
- · Centerpiece: Yes

Light characteristics

· Color rendering index (CRI): 80

Miscellaneous

- · Especially designed for: Bathroom
- Style: Contemporary

Product dimensions and weight

- · Net weight: 0.396 kg
- · Height: 17 cm
- · Length: 12 cm
- · Width: 15 cm

Service

Warranty: 1 year(s)

Technical specifications

- Lamp lifetime up to: 20,000
- · Total lumen output fixture: 600
- · Bulb technology: LED
- Light color: 3000-6500
- · Mains power: 220-240 V
- Energy class included light source: built in LED + bulb of class A+
- IP code: IP44 | Wire-protected and splash-proof

Packaging dimensions and weight

- EAN/UPC product: 8720169212039
- Net weight: 0.4 kg
- · Gross weight: 0.88 kg
- · Height: 13.3 cm
- · Length: 21.2 cm
- Width: 13 cm



Issue date: 2025–11-05

Version: 0.63

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any comparing offer and does not form part of any

information included nerein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips