

PHILIPS

IP44 dust and water-resistant two-way light wall washer

myLiving

10W; 850 lumen; In-built LED;

Beautiful reddish-brown color inside the fixture

Powder-coated premium aluminium fixture;

Tunable white (warm white, natural white and cool white)

919215851203



Decorate walls with beautiful fixture and human-centric lighting

This exquisite decorative wall washer creates a beautiful up and down lighting effect, that adds romantic & harmonious ambience to your room as well as your exterior surroundings. IP44 protection makes it perfect for use in moist areas as well

Light modes

- Tunable warm to cool white and preset modes

Highlights

Tunable warm to cool white and preset modes

Choose from a wide range of energizing cool white to soft warm

white, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.

Specifications

Bulb characteristics

- Intended use: Indoor/Outdoor

Bulb dimensions

- Height: 12.7 cm

Design and finishing

- Color: Black outside and Reddish Brown inside
- Material: Metal

Extra feature/accessory incl.

- 4 light recipes: No
- 5 years warranty on the LED module: No
- Adjustable height: No
- Adjustable spot head: No
- Batteries included: No
- Bi-directional light beams: No
- Candle light effect: No
- Centerpiece: No
- Choose your color: No
- Clamp included: Yes
- Color changing (LED): Yes
- Day-and-night sensor: No
- Defined light beams: No
- Fully weatherproof: No
- Hue bridge included: No
- Hue Switch: No
- Hue Switch Included: No
- LED integrated: Yes
- Perfectly suited for ambience creation: Yes
- Premium quality material: Yes
- Centerpiece: Yes

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Bathroom
- Style: Contemporary

Product dimensions and weight

- Net weight: 0.494 kg
- Height: 12.7 cm
- Length: 20 cm
- Width: 9.5 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lamp lifetime up to: 20,000 hour(s)
- Lumen output bulb included: 850 lm
- Total lumen output fixture: 850
- Bulb technology: LED
- Light color: Tunable white (warm white, natural white and cool white on switch toggle)
- Mains power: 220-240 V
- Energy class included light source: built in LED + bulb of class A+
- IP code: IP44

Packaging dimensions and weight

- EAN/UPC – product: 8720169211452
- Net weight: 0.49 kg
- Gross weight: 0.76 kg
- Height: 14 cm
- Length: 23.7 cm
- Width: 10.6 cm



Issue date: 2025-06-06
Version: 0.59

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com