

PHILIPS

Outdoor Pedestal

myGarden

12W; Warm White; Anthracite color; Lumen: 812; In-built LED

Creates stunning light pattern on the ground;

IP65 (dust-proof and water-resistant);

Premium aluminium material

919215851224



Creates stunning light pattern on the ground

Vibe range of outdoor pedestals will lend a flamboyant charm to your outdoors with unique and striking patterns which they create on the ground. Mesmerize people walking through your outdoors with these stylish outdoor lights that come in different form factors – conical, round and square base. These are sure to create awesome ‘vibes’ for you, your family and your guests.

Bring design into your garden

- Stylish contemporary designs for your garden

Highlights

Stylish contemporary designs for your garden

The contemporary designs by Philips are stylish but understated, beautiful

by day or night without overwhelming your garden or terrace. Thereas a full range of lights to choose from, so

thereas bound to be one to match your outside space and taste.

Specifications

Bulb characteristics

- Intended use: Outdoor

Design and finishing

- Color: Grey
- Material: Metal

Extra feature/accessory incl.

- 4 light recipes: No
- 5 years warranty on the LED module: No
- Adjustable height: No
- Adjustable spot head: No
- Anti rust anti dust: Yes
- Batteries included: No
- Bi-directional light beams: No
- Candle light effect: No
- Centerpiece: No
- Charger base included: No
- Choose your color: No
- Clamp included: Yes
- click!FIX mounting: No
- Color changing (LED): No
- Color changing (PowerLED): No
- compatible with all dimmers: No
- Compatible with most dimmers: No
- Day-and-night sensor: No
- Defined light beams: No
- Diffused light effect: No
- Dimmable: No
- Dimmable with Hue app and switch: No
- Dimmable with remote control: No
- Dimmer and on/off switch on article: No
- Dimmer on article: No
- Double on/off on article: No
- E26 Socket adapter: No
- Easy bulb swap: No
- FFP - Frustration Free Pack: No
- Flexible arm: No
- Fluorescent lamp(s) included: No
- Fully weatherproof: Yes
- Halogen lamp(s) included: No
- Hue bridge included: No
- Hue Switch: No
- Hue Switch Included: No
- LED integrated: Yes
- LED lamp(s) included: No
- Made for LED only: Yes
- Magnetic cover: No
- Motion & day-and-night sensor: No
- Motion sensor: No
- Perfectly suited for ambiance creation: Yes
- Pivotal arm(left-right): No
- Pivotal head (left-right): No
- Portable: No
- Power adapter included: No

- PowerLED lamp(s) included: No
- Premium quality material: Yes
- Protection sleeve included: No
- Remote control included: No
- Resistant high quality material: No
- Rotates freely in any direction: No
- Solar Energy: No
- Tilttable head (up-down): No
- Warm White Light: Yes
- Waterproof: Yes
- Centerpiece: No
- Centerpiece: No
- Centerpiece: No

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Expressive
- EyeComfort: No

Product dimensions and weight

- Net weight: 1.583 kg
- Height: 81.5 cm
- Height maximum: 815 mm
- Height minimum: 120 mm
- Length: 12 cm
- Width: 12 cm
- Height: 32.09 inch
- Length: 4.72 inch
- Width: 4.72 inch
- Product height range: 120 mm to 815 mm

Service

- Warranty: 1 year(s)

Technical specifications

- Total lumen output fixture: 912
- Bulb technology: LED
- Light color: Warm white light
- Mains power: 220–240 V
- Fixture dimmable: No
- Energy class included light source: Built in LED
- IP code: IP65
- Light source replaceable: No

Packaging dimensions and weight

- EAN/UPC - product: 8720169267534
- Net weight: 1.58 kg
- Gross weight: 1.95 kg
- Height: 82.5 cm
- Length: 12.8 cm
- Width: 12.8 cm



Issue date: 2026-05-13
Version: 0.177

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com