






	Power (W)	Lumen output (lm)	Efficacy (lm/W)	Energy efficacy class	CCT (K)	UGR	Class	kg
RC136B G4 34_43_57S/830 PSD W30L120 OC	23*/29/38.5	3400*/4300/5700	148*/148/148	C	3000	19	II	3.0
RC136B G4 34_43_57S/830 PSD W60L60 OC	23*/29/38.5	3400*/4300/5700	148*/148/148	C	3000	19	II	3.1
RC136B G4 36_45_60S/840 PSD W30L120 OC	23*/29/38.5	3600*/4500/6000	157*/155/156	C	4000	19	II	3.0
RC136B G4 36_45_60S/840 PSD W60L60 OC	23*/29/38.5	3600*/4500/6000	157*/155/156	C	4000	19	II	3.1
RC136B G4 36_45_60S/840 PSU W60L60 NOC	23*/29/38.5	3600*/4500/6000	157*/155/156	C	4000	25	II	3.1
RC136B G4 36_45_60S/840 PSU W60L60 OC	23*/29/38.5	3600*/4500/6000	157*/155/156	C	4000	19	II	3.1
RC136B G4 40S/830 WIA W60L60 OC	27.5	4000	145	C	3000	19	II	3.1
RC136B G4 43S/840 WIA W30L120 OC	27.5	4300	156	C	4000	19	II	3.0
RC136B G4 43S/840 WIA W60L60 OC	27.5	4300	156	C	4000	19	II	3.1

* Default setting










Available as accessory (Need to purchase separately)

<p>Suspension set: 911401809387 RC159Z Suspension set SME-4 WH 911401809487 RC159Z Suspension set SME-3 WH</p> 	<p>Surface mounted set: 911401807787 RC159Z SMB W60L60 911401807987 RC159Z SMB W30L120</p> 	<p>Plaster ceiling set: 911401809287 RC159Z Plaster Ceiling SMB-PLC</p> 
---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

 **Quick-connectors**

<p>PSU/PSD/WIA</p>  <p>1a</p>	<p>PSD</p>  <p>1b</p>
<p>PSD Touch & Dim</p>  <p>1c</p>	<p>PSU/WIA</p> 

Compatible with Wieland W3, W5 connector:



Locking device, order separately
 05.587.3156.1 Lock (G)ST18 SW


 The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEEE electrical regulations or the national requirements.

Lumen Selection on driver



PSU


DIP Switch



Pin	3000K CCT (lumen)	4000K CCT (lumen)	Power
Low	3400 lm*	3600 lm*	23 W*
Medium	4300 lm	4500 lm	29 W
High	5700 lm	6000 lm	38.5 W

* Default setting



PSD






Pin1	Pin2	Pin3	3000K CCT (lumen)	4000K CCT (lumen)	Power
OFF	OFF	ON	3400 lm*	3600 lm*	23 W*
OFF	ON	ON	4300 lm	4500 lm	29 W
ON	OFF	OFF	5700 lm	6000 lm	38.5 W



Safety cable





VPC (Visible Profile Ceiling)








The luminaire shall not be covered with thermal insulation or similar material under any circumstance.



PCV (Plaster ceiling version)



Module	A (mm)	B (mm)
RC136B W60L60	580	580
RC136B W30L120	280	1180








3

4



Surface mounted

Optional with
911401807787:RC159Z SMB W60L60
911401807987:RC159Z SMB W30L120
(Needs to be purchased separately)



Dimensions in mm






	A	B	C	D	E	F
W60L60	615.5	615.5	335.5	580	/	/
W30L120	1215.5	315.5	855.5	280	1180	210



Emergency Lighting (EL) Kit

Optional with
912401483602
EM300V ELB_ELP3 kit LV 3.6V 4900mAh LIB

(Need to purchase separately)



1

2

3

Optional

12NC


912401483602

Description

EM300V ELB_ELP3 kit LV 3.6V 4900mAh LIB


Emergency pack is not provided.

1x



Products compatible with emergency lighting functionality.

12NC	Description	EOC	SKU
911401840687	RC136B G4 34_43_57S/830 PSD W30L120 OC	872016976411899	108403763
911401840787	RC136B G4 34_43_57S/830 PSD W60L60 OC	872016976412599	108403764
911401840887	RC136B G4 36_45_60S/840 PSD W30L120 OC	872016976413299	108403765
911401840987	RC136B G4 36_45_60S/840 PSD W60L60 OC	872016976414999	108403766
911401841087	RC136B G4 36_45_60S/840 PSU W60L60 NOC	872016976415699	108403767
911401841187	RC136B G4 36_45_60S/840 PSU W60L60 OC	872016976416399	108403768
911401841287	RC136B G4 40S/830 WIA W60L60 OC	872016976417099	108403769
911401841387	RC136B G4 43S/840 WIA W30L120 OC	872016976418799	108403770
911401841487	RC136B G4 43S/840 WIA W60L60 OC	872016976419499	108403771



Rated lumen output in emergency mode: min 300lm

Can be assembled in the luminaires in table 1.
After installing emergency pack, customers shall ensure that the emergency light comply with IEC60598-2-22. and maximum ambient temperature shall be less than 30C.









Suspension

Optional with
911401809387 RC159Z Suspension set SME-4 WH
911401809487 RC159Z Suspension set SME-3 WH

PSU/ WIA

911401809487
RC159Z Suspension set SME-3 WH
(Needs to be purchased separately)







60227 IEC52
2 x 0.75-1.5 mm²
Ø 6-9 mm

1a



PSD

911401809387
RC159Z Suspension set SME-4 WH
(Needs to be purchased separately)





60227 IEC52
4 x 0.75-1.5 mm²
Ø 6-9 mm

1b




2

3



Inrush current	PSU			PSD			WIA
	W60L60	23 W	29 W	38.5 W	23 W	29 W	38.5 W
W30L120	23 W	29 W	38.5 W	23 W	29 W	38.5 W	27.5 W
Electrical characteristise							
$I_{max}(A)$	25			5.33			4.9
$T_{ref}(us)$	150			40			56
No. of luminaires max.							
MCB							
B-10 A	24			46			15
B-16A	38			73			24
C-10 A	40			46			25
C-16A	64			73			40

Inrush current



- The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEEE electrical regulations or the national requirements.
- The light source of this luminaire is not replaceable; when the light source reaches its end of life the whole luminaire shall be replaced.
- Luminaires not suitable for covering with thermally insulating material.
- Luminaire must not be used or stored in corrosive environment where hazardous materials such as Sulphur, Chlorine, Phthalates, etc, are present.
- If the external flexible cable or cord of this luminaire is damaged, it shall be exclusively replaced by the manufacturer or his service agent or a similar qualified person in order to avoid a hazard.

ATTENTION
OBSERVE PRECAUTIONS
FOR HANDLING
ELECTROSTATIC
SENSITIVE
DEVICES

