



1 x 9290020252 G120 2700K 7W

1 x 806 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.41
Service downward 0.59

CIE flux code 23 48 74 59 100

UGRcen (4Hx8H, 0.25H) 27

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.30	0.10	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.60	0.35	0.33	0.32	0.31	0.31	0.23	0.20	0.16	0.17	0.13	0.09	0.09
0.80	0.44	0.41	0.40	0.39	0.38	0.30	0.26	0.21	0.22	0.18	0.12	0.12
1.00	0.51	0.47	0.47	0.45	0.44	0.36	0.31	0.26	0.26	0.22	0.15	0.15
1.25	0.58	0.53	0.54	0.52	0.50	0.42	0.36	0.31	0.31	0.26	0.18	0.18
1.50	0.64	0.58	0.59	0.57	0.54	0.47	0.40	0.35	0.34	0.30	0.21	0.21
2.00	0.73	0.65	0.67	0.64	0.61	0.54	0.47	0.42	0.40	0.36	0.26	0.26
2.50	0.80	0.70	0.73	0.69	0.66	0.59	0.52	0.47	0.44	0.41	0.30	0.30
3.00	0.85	0.74	0.78	0.73	0.69	0.63	0.55	0.51	0.47	0.44	0.33	0.33
4.00	0.91	0.79	0.84	0.78	0.74	0.69	0.60	0.56	0.52	0.49	0.37	0.37
5.00	0.96	0.82	0.88	0.82	0.77	0.72	0.63	0.60	0.55	0.52	0.40	0.40

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	15972	14492	13694	13441	13694	14492	15972
50.0	16535	14869	13984	13706	13984	14869	16535
55.0	17190	15319	14338	14032	14338	15319	17190
60.0	17942	15839	14752	14415	14752	15839	17942
65.0	18767	16403	15200	14829	15200	16403	18767
70.0	19704	17039	15704	15295	15704	17039	19704
75.0	20765	17747	16261	15810	16261	17747	20765
80.0	21969	18532	16872	16372	16872	18532	21969
85.0	23402	19446	17579	17021	17579	19446	23402
90.0	25120	20510	18389	17763	18389	20510	25120

(cd/m²)

2019-02-26