


1 x TForce 26W 3000K 929002485000

1 x 4200 lm

Polar intensity diagram




Light output ratio 1.00
Service upward 0.52
Service downward 0.48

CIE flux code 32 55 78 48 100

UGRcen (4Hx8H, 0.25H) 30

Quantity estimation diagram




Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.80	0.80	0.70	0.70	0.70
0.60	0.37	0.36	0.35	0.34	0.33	0.26	0.22	0.18	0.19	0.15	0.10	0.37	0.36	0.35	0.34	0.26
0.80	0.46	0.44	0.43	0.41	0.40	0.33	0.28	0.24	0.23	0.20	0.13	0.46	0.44	0.43	0.41	0.33
1.00	0.54	0.50	0.49	0.47	0.46	0.39	0.33	0.28	0.27	0.24	0.16	0.54	0.50	0.49	0.47	0.39
1.25	0.61	0.56	0.56	0.53	0.51	0.44	0.38	0.33	0.31	0.28	0.18	0.61	0.56	0.56	0.53	0.44
1.50	0.67	0.60	0.61	0.58	0.56	0.49	0.41	0.37	0.34	0.31	0.21	0.67	0.60	0.61	0.58	0.49
2.00	0.75	0.67	0.69	0.65	0.62	0.56	0.47	0.43	0.39	0.36	0.24	0.75	0.67	0.69	0.65	0.56
2.50	0.81	0.72	0.74	0.70	0.66	0.61	0.52	0.48	0.43	0.40	0.27	0.81	0.72	0.74	0.70	0.61
3.00	0.86	0.75	0.78	0.73	0.69	0.64	0.55	0.51	0.45	0.43	0.29	0.86	0.75	0.78	0.73	0.64
4.00	0.92	0.80	0.83	0.78	0.74	0.69	0.59	0.56	0.49	0.47	0.32	0.92	0.80	0.83	0.78	0.69
5.00	0.96	0.82	0.87	0.81	0.76	0.73	0.62	0.59	0.51	0.49	0.34	0.96	0.82	0.87	0.81	0.73

Ceiling mounted

UGR diagram



Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	28727	27798	27460	29691	35426	40840	42727
50.0	30193	28735	27141	26733	31234	38199	40743
55.0	34015	31908	28800	26086	27283	34885	38122
60.0	39191	36691	32490	27327	24702	30617	34638
65.0	44353	41780	37374	30626	24283	25671	30129
70.0	48048	45439	41767	35253	25764	20984	24392
75.0	50425	47796	44482	39060	29175	17662	17054
80.0	51334	48784	45931	41233	32200	16281	9844
85.0	51638	49027	46275	42017	33495	16171	4958
90.0	54737	51869	48912	44535	35809	17369	6108

(cd/m²)

2021-02-04