


1 x Tforce 26W 4000K 929002485100

1 x 4500 lm

Polar intensity diagram




Light output ratio 1.00
Service upward 0.52
Service downward 0.48

CIE flux code 32 55 78 48 100

UGRcen (4Hx8H, 0.25H) 30

Quantity estimation diagram




Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.80	0.80	0.70	0.70	0.70	0.70	0.30	0.10	0.10	0.10	0.00	0.00
0.80	0.50	0.50	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
1.00	0.30	0.10	0.10	0.10	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
1.25	0.37	0.36	0.35	0.34	0.33	0.26	0.22	0.18	0.19	0.15	0.10	0.10
1.50	0.46	0.44	0.43	0.41	0.40	0.33	0.28	0.24	0.23	0.20	0.13	0.13
1.75	0.54	0.50	0.49	0.47	0.46	0.39	0.33	0.28	0.27	0.24	0.16	0.16
2.00	0.61	0.56	0.56	0.53	0.51	0.44	0.38	0.33	0.31	0.28	0.18	0.18
2.50	0.67	0.60	0.61	0.58	0.56	0.49	0.41	0.37	0.34	0.31	0.21	0.21
3.00	0.75	0.67	0.69	0.65	0.62	0.56	0.47	0.43	0.39	0.36	0.24	0.24
3.50	0.81	0.72	0.74	0.70	0.66	0.61	0.52	0.48	0.43	0.40	0.27	0.27
4.00	0.86	0.75	0.78	0.73	0.69	0.64	0.55	0.51	0.45	0.43	0.29	0.29
4.50	0.92	0.80	0.83	0.78	0.74	0.69	0.59	0.56	0.49	0.47	0.32	0.32
5.00	0.96	0.82	0.87	0.81	0.76	0.73	0.62	0.59	0.51	0.49	0.34	0.34

Ceiling mounted

UGR diagram



Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	30780	29783	29421	31812	37955	43757	45779
50.0	32350	30787	29079	28642	33465	40928	43654
55.0	36445	34187	30857	27949	29232	37377	40844
60.0	41991	39312	34810	29279	26467	32804	37113
65.0	47521	44764	40044	32813	26018	27504	32280
70.0	51481	48685	44751	37772	27605	22482	26132
75.0	54027	51209	47660	41850	31258	18923	18274
80.0	55000	52268	49212	44177	34499	17443	10546
85.0	55327	52529	49580	45020	35887	17325	5314
90.0	58647	55574	52405	47716	38366	18612	6544

(cd/m²)

2021-02-04