



1 x Tforce SOX 929002497000**1 x 5000 lm****Polar intensity diagram**

Light output ratio 1.00
 Service upward 0.22
 Service downward 0.78


CIE flux code 33 60 82 78 100

UGRcen (4Hx8H, 0.25H) 30

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80			0.70			0.50			0.30		
	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30
0.60	0.39	0.37	0.37	0.37	0.36	0.28	0.26	0.21	0.24	0.20	0.17	0.17
0.80	0.48	0.46	0.46	0.45	0.44	0.36	0.33	0.28	0.31	0.26	0.22	0.22
1.00	0.56	0.52	0.54	0.52	0.50	0.42	0.39	0.34	0.36	0.31	0.27	0.27
1.25	0.64	0.59	0.61	0.58	0.56	0.48	0.45	0.40	0.41	0.37	0.31	0.31
1.50	0.70	0.64	0.67	0.64	0.61	0.53	0.50	0.44	0.46	0.41	0.35	0.35
2.00	0.80	0.71	0.75	0.72	0.68	0.61	0.57	0.52	0.53	0.48	0.42	0.42
2.50	0.86	0.76	0.81	0.77	0.73	0.67	0.62	0.57	0.57	0.53	0.46	0.46
3.00	0.91	0.80	0.86	0.81	0.76	0.71	0.66	0.62	0.61	0.57	0.50	0.50
4.00	0.98	0.84	0.92	0.86	0.81	0.76	0.71	0.67	0.66	0.62	0.55	0.55
5.00	1.02	0.87	0.96	0.90	0.84	0.80	0.74	0.71	0.69	0.66	0.58	0.58

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	27784	26964	26426	26072	26357	28372	32953
50.0	27583	26636	25915	25282	25131	26820	31388
55.0	27524	26460	25540	24582	23980	25185	29348
60.0	27658	26415	25280	24015	22843	23582	27651
65.0	27717	26420	25166	23669	21887	21849	24952
70.0	28145	26669	25225	23469	21146	20179	21572
75.0	28473	26860	25322	23472	20589	18518	17339
80.0	29009	27246	25575	23547	20198	17084	12718
85.0	29368	27599	25889	23725	19995	15717	5797
90.0	29911	27976	26231	24131	19960	15266	1183

(cd/m²)

2020-12-18