




Candle 25W 2700K E27P45 9290013456

1 x 250 lm

Polar intensity diagram**Quantity estimation diagram****UGR diagram**

Light output ratio 1.00
Service upward 0.51
Service downward 0.49

CIE flux code 9 34 66 49 100

UGRcen (4Hx8H, 0.25H) 23

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.80	0.80	0.70	0.70	0.70
0.50	0.50	0.50	0.50	0.50	0.50	0.30	0.30	0.10	0.00	0.00	0.00	0.50	0.50	0.50	0.50	0.30
0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.10	0.10	0.10	0.10	0.00
0.60	0.31	0.29	0.28	0.27	0.26	0.19	0.15	0.11	0.11	0.08	0.02	0.31	0.29	0.28	0.27	0.19
0.80	0.39	0.37	0.35	0.34	0.33	0.25	0.20	0.15	0.16	0.12	0.05	0.39	0.37	0.35	0.34	0.25
1.00	0.46	0.43	0.42	0.41	0.39	0.31	0.25	0.20	0.19	0.15	0.07	0.46	0.43	0.42	0.41	0.31
1.25	0.54	0.49	0.49	0.47	0.45	0.37	0.30	0.25	0.23	0.19	0.10	0.54	0.49	0.49	0.47	0.37
1.50	0.60	0.54	0.54	0.52	0.49	0.41	0.34	0.29	0.27	0.23	0.12	0.60	0.54	0.54	0.52	0.41
2.00	0.69	0.61	0.62	0.59	0.56	0.49	0.40	0.35	0.32	0.28	0.16	0.69	0.61	0.62	0.59	0.49
2.50	0.75	0.66	0.68	0.64	0.61	0.54	0.45	0.40	0.36	0.32	0.20	0.75	0.66	0.68	0.64	0.54
3.00	0.80	0.70	0.72	0.68	0.64	0.58	0.48	0.44	0.39	0.36	0.22	0.80	0.70	0.72	0.68	0.58
4.00	0.87	0.75	0.79	0.74	0.69	0.64	0.53	0.50	0.43	0.40	0.26	0.87	0.75	0.79	0.74	0.64
5.00	0.92	0.79	0.83	0.77	0.72	0.68	0.57	0.53	0.47	0.44	0.29	0.92	0.79	0.83	0.77	0.68

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	4700	4700	4700	4700	4700	4700	4700
50.0	5110	5110	5110	5110	5110	5110	5110
55.0	5484	5484	5484	5484	5484	5484	5484
60.0	5832	5832	5832	5832	5832	5832	5832
65.0	6145	6145	6145	6145	6145	6145	6145
70.0	6448	6448	6448	6448	6448	6448	6448
75.0	6732	6732	6732	6732	6732	6732	6732
80.0	7004	7004	7004	7004	7004	7004	7004
85.0	7268	7268	7268	7268	7268	7268	7268
90.0	7527	7527	7527	7527	7527	7527	7527

(cd/m²)

SL25765-1

2017-03-02