


1 x GU10 3.1W2700K 36D 9290012175

1 x 240 lm




Light output ratio 1.00
Service upward 0.00
Service downward 1.00

Imax 469 cd



BS ($\frac{1}{2}I_{max}$) 13°, 18°

BS ($\frac{1}{2}E_0$) 12°, 17°

SL20593



Visual impact diagram



2016-01-06