


1 x GU10 4.6W2700K 36D 9290012152

1 x 395 lm


Polar intensity diagram




Light output ratio 1.08
Service upward 0.00
Service downward 1.08

Imax 718 cd
BS ($1/2 I_{max}$) 16°, 20°
BS ($1/2 E_0$) 15°, 18°


Cartesian intensity diagram



Visual impact diagram



Beam diagram



SL20593

2016-01-06