



MR16 5.5W 3000K 24D 929001146700

1 x 425 lm


Polar intensity diagram



Cartesian intensity diagram



Beam diagram




Light output ratio 1.00
Service upward 0.00
Service downward 1.00

Imax 1888 cd

VBA 2 x 20°
BS ($1/2 I_{max}$) 2 x 11°
BS ($1/2 E_0$) 2 x 11°

K5

Visual impact diagram



RZ080504

2015-01-06