


929001823704 1 x TLED InstantFit T5 HE 3ft 1500


1 x 1500 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.26
 Service downward 0.74


CIE flux code 35 63 84 74 100

UGRcen (4Hx8H, 0.25H) 26

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.40	0.38	0.38	0.37	0.36	0.29	0.26	0.22	0.24	0.20	0.17	
0.80	0.49	0.46	0.47	0.45	0.44	0.36	0.34	0.29	0.31	0.26	0.22	
1.00	0.57	0.53	0.54	0.52	0.51	0.43	0.39	0.34	0.36	0.32	0.26	
1.25	0.65	0.60	0.61	0.59	0.57	0.49	0.45	0.40	0.42	0.37	0.31	
1.50	0.71	0.64	0.67	0.64	0.62	0.54	0.50	0.45	0.46	0.42	0.35	
2.00	0.80	0.72	0.76	0.72	0.69	0.62	0.57	0.53	0.52	0.48	0.41	
2.50	0.87	0.77	0.82	0.77	0.73	0.67	0.62	0.58	0.57	0.53	0.46	
3.00	0.92	0.80	0.86	0.81	0.77	0.71	0.66	0.62	0.60	0.57	0.49	
4.00	0.98	0.85	0.92	0.86	0.81	0.77	0.71	0.67	0.65	0.62	0.53	
5.00	1.02	0.88	0.96	0.90	0.84	0.80	0.74	0.71	0.68	0.65	0.56	

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	10233	10215	10272	10474	10987	12139	14762
50.0	9954	9918	9921	10050	10456	11521	14367
55.0	9722	9660	9624	9655	9923	10827	13824
60.0	9531	9487	9374	9319	9400	10091	13236
65.0	9386	9319	9168	9029	8920	9275	12385
70.0	9298	9227	9041	8818	8510	8412	11305
75.0	9306	9155	9015	8708	8204	7551	9803
80.0	9367	9261	9067	8673	7995	6698	7621
85.0	9470	9362	9146	8715	7964	6066	4491
90.0	9624	9512	9325	8952	8132	6043	2601

(cd/m²)

2017-11-14