



T5 26W 4000K 9290019086 1 x**1 x 3900 lm****Polar intensity diagram**

Light output ratio 1.00
 Service upward 0.24
 Service downward 0.76


CIE flux code 37 65 86 76 100

UGR_{cen} (4Hx8H, 0.25H) 28

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.50	0.50	0.50	0.50	0.50	0.50	0.30	0.30	0.10	0.30	0.10	0.00	0.00
0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.60	0.41	0.39	0.39	0.38	0.37	0.30	0.28	0.23	0.26	0.22	0.18	0.18
0.80	0.50	0.47	0.48	0.47	0.45	0.38	0.35	0.30	0.32	0.28	0.24	0.24
1.00	0.58	0.54	0.55	0.54	0.52	0.44	0.41	0.36	0.38	0.34	0.28	0.28
1.25	0.66	0.61	0.63	0.60	0.58	0.51	0.47	0.42	0.43	0.39	0.33	0.33
1.50	0.72	0.66	0.69	0.66	0.63	0.56	0.52	0.47	0.48	0.44	0.37	0.37
2.00	0.82	0.73	0.77	0.73	0.70	0.64	0.59	0.54	0.54	0.51	0.44	0.44
2.50	0.88	0.78	0.83	0.79	0.75	0.69	0.64	0.60	0.59	0.56	0.48	0.48
3.00	0.93	0.81	0.88	0.83	0.78	0.73	0.68	0.64	0.62	0.59	0.52	0.52
4.00	0.99	0.86	0.94	0.88	0.83	0.78	0.72	0.69	0.67	0.64	0.56	0.56
5.00	1.04	0.89	0.97	0.91	0.85	0.82	0.76	0.73	0.70	0.67	0.59	0.59

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	22186	21549	21629	22470	24238	27289	32338
50.0	21560	20745	20669	21372	23035	26087	31487
55.0	21022	20010	19756	20286	21793	24769	30462
60.0	20588	19352	18889	19204	20485	23277	29148
65.0	20250	18764	18063	18122	19107	21587	27468
70.0	20021	18255	17283	17036	17637	19625	25189
75.0	19902	17830	16562	15969	16102	17386	22072
80.0	19924	17533	15957	15000	14607	14960	17691
85.0	20106	17425	15589	14331	13485	12904	11844
90.0	20491	17657	15747	14474	13685	13364	18981

(cd/m²)

2018-03-26