


1 x TLED 26W 3000K 9290035324

1 x 3700 lm

Polar intensity diagram




Light output ratio 1.00
 Service upward 0.27
 Service downward 0.73

CIE flux code 35 63 84 73 100

UGRcen (4Hx8H, 0.25H) 28

Quantity estimation diagram




Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80 0.80				0.70 0.70				0.50 0.50			
	0.80	0.50	0.30	0.10	0.80	0.50	0.30	0.10	0.80	0.50	0.30	0.10
0.60	0.40	0.38	0.38	0.37	0.36	0.29	0.26	0.22	0.24	0.20	0.16	0.16
0.80	0.49	0.46	0.47	0.45	0.44	0.36	0.33	0.28	0.31	0.26	0.22	0.22
1.00	0.57	0.53	0.54	0.52	0.50	0.43	0.39	0.34	0.36	0.32	0.26	0.26
1.25	0.65	0.59	0.61	0.59	0.57	0.49	0.45	0.40	0.41	0.37	0.31	0.31
1.50	0.71	0.64	0.67	0.64	0.61	0.54	0.50	0.45	0.45	0.41	0.35	0.35
2.00	0.80	0.72	0.76	0.72	0.68	0.62	0.57	0.52	0.52	0.48	0.41	0.41
2.50	0.87	0.77	0.82	0.77	0.73	0.67	0.62	0.58	0.56	0.53	0.45	0.45
3.00	0.91	0.80	0.86	0.81	0.77	0.71	0.65	0.61	0.60	0.57	0.48	0.48
4.00	0.98	0.85	0.92	0.86	0.81	0.76	0.70	0.67	0.64	0.61	0.53	0.53
5.00	1.02	0.88	0.96	0.89	0.84	0.80	0.73	0.70	0.67	0.65	0.55	0.55

Ceiling mounted

UGR diagram



Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	22102	22199	23086	23984	25871	29904	36468
50.0	21485	21510	22366	23069	24794	28854	35915
55.0	20946	20923	21777	22231	23716	27682	35140
60.0	20590	20475	21283	21455	22645	26334	33966
65.0	20186	20048	20886	20769	21646	24838	32308
70.0	20101	19862	20659	20212	20707	23091	29762
75.0	20075	19794	20628	19869	20002	21256	26138
80.0	20111	19751	20591	19639	19582	19322	20264
85.0	20376	19962	20866	19739	19541	17925	11568
90.0	20863	20416	21448	20274	20205	19106	2400

(cd/m²)

s23030033a

2023-04-13