



# All-in-one solar post top up to 5000lm with 3CCTs selectable

## Essential SmartBright Solar Post Top

A range of solar all in one post top with unique feature of selectable color temperature

### Benefits

- Resistant to shock and vibration
- Suitable for wide applications upto 5000 lumen pack
- With selectable color temperature, creates outdoor ambience easily through a remote control
- Sensors ensure light on demand and optimize battery performance
- High efficacy ensures bright light yet with low power consumption leading to higher autonomy

### Features

- Bright functional light output upto 5000 lumen
- Color temperature is selectable.
- Microwave sensor based dimming profile
- High luminous efficacy up-to 165 lm/watt to maximize battery performance
- Durable polycarbonate material housing

### Application


- Landscaped areas
- Garden
- Walkways

### Warnings and Safety

- Install the product in a place with adequate sunlight without shades of trees, building, walls etc. for faster charging of battery

# Essential SmartBright Solar Post Top

## Dimensional drawing



Light Technical	
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	70
Operating and Electrical	
Battery type	Lithium Ferro Phosphate
Battery voltage	3.2 V
Grid connection type	Off grid
Panel type	Poly crystalline
Panel voltage	4.5 V
Controls and Dimming	
Dimmable	Yes
Configurability	Not configurable
Solar dimming profile	Pre-configured
Mechanical and Housing	
Battery location	In built
Ingress protection code	IP65
Approval and Application	
Ambient temperature range	0 °C to 55 °C

## Operating and Electrical

Order Code	Full Product Name	Battery ampere hour	Panel peak wattage
66936299	BPC010 LED20/MCT Solar post top	10.8 Ah	13 W
66937999	BPC010 LED30/MCT Solar post top	14.4 Ah	13 W
66938699	BPC010 LED40/MCT Solar post top	14.4 Ah	15 W
66939399	BPC010 LED50/MCT Solar post top	21.6 Ah	20 W
61016699	BPC010 LED20/MCT Solar post top Pro	10.8 Ah	13 W
61017399	BPC010 LED30/MCT Solar post top Pro	14.4 Ah	13 W
61018099	BPC010 LED40/MCT Solar post top Pro	14.4 Ah	15 W
61019799	BPC010 LED50/MCT Solar post top Pro	21.6 Ah	20 W

## Mechanical and Housing

Order Code	Full Product Name	Housing Color	Overall height	Overall length	Overall width
66936299	BPC010 LED20/MCT Solar post top	Grey	123 mm	420 mm	420 mm
66937999	BPC010 LED30/MCT Solar post top	Grey	123 mm	420 mm	420 mm
66938699	BPC010 LED40/MCT Solar post top	Grey	123 mm	420 mm	420 mm
66939399	BPC010 LED50/MCT Solar post top	Grey	137 mm	520 mm	520 mm

Order Code	Full Product Name	Housing Color	Overall height	Overall length	Overall width
61016699	BPC010 LED20/MCT Solar post top Pro	Gray	123 mm	420 mm	420 mm
61017399	BPC010 LED30/MCT Solar post top Pro	Gray	123 mm	420 mm	420 mm
61018099	BPC010 LED40/MCT Solar post top Pro	Gray	123 mm	420 mm	420 mm
61019799	BPC010 LED50/MCT Solar post top Pro	Gray	137 mm	520 mm	520 mm

## Essential SmartBright Solar Post Top

