



Solar post top

Essential SmartBright solar post top

A range of solar all in one post top lantern with unique feature of selectable color temperature

Benefits

- Resistant to shock and vibration.
- Suitable for wide applications upto 5000 lumen pack
- With selectable color temperature, creates outdoor ambience easily through a remote control
- Sensors ensure light on demand and optimize battery performance
- High efficacy ensures bright light yet with low power consumption leading to higher autonomy

Features

- Durable polycarbonate based housing.
- Bright functional light output upto 5000 lumen
- Color temperature is selectable.
- Microwave sensor based dimming profile
- High luminous efficacy up-to 165 lm/watt to maximize battery performance

Application

- Landscaped areas
- Garden

Warnings and Safety

- Install the product in a place with adequate sunlight without shades of trees, building, walls etc. for faster charging of battery

Essential SmartBright solar post top

Versions



Essential SmartBright Solar
Posttop BPC010

Light Technical	
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	70
Operating and Electrical	
Battery type	Lithium Ferro Phosphate
Battery voltage	3.2 V
Grid connection type	Off grid
Panel type	Poly crystalline
Panel voltage	4.5 V
Controls and Dimming	
Dimmable	Yes
Configurability	Not configurable
Solar dimming profile	Pre-configured
Mechanical and Housing	
Battery location	In built
Housing Color	Grey
Ingress protection code	IP65
Approval and Application	
Ambient temperature range	0 °C to 55 °C

Operating and Electrical

Order Code	Full Product Name	Battery ampere hour	Panel peak wattage
911401863102	BPC010 LED20/MCT Solar post top	10.8 Ah	13 W
911401863202	BPC010 LED30/MCT Solar post top	14.4 Ah	13 W
911401863302	BPC010 LED40/MCT Solar post top	14.4 Ah	15 W
911401863402	BPC010 LED50/MCT Solar post top	21.6 Ah	20 W

Mechanical and Housing

Order Code	Full Product Name	Overall height	Overall length	Overall width
911401863102	BPC010 LED20/MCT Solar post top	123 mm	420 mm	420 mm
911401863202	BPC010 LED30/MCT Solar post top	123 mm	420 mm	420 mm

Order Code	Full Product Name	Overall height	Overall length	Overall width
911401863302	BPC010 LED40/MCT Solar post top	123 mm	420 mm	420 mm
911401863402	BPC010 LED50/MCT Solar post top	137 mm	520 mm	520 mm

Essential SmartBright solar post top

