



Most affordable, dimmable plastic A19 lamp

Contractor-grade Plastic (Dimmable) A-Shape Lamps

Plastic A19 offering dimmability and a lifetime over 15,000 hours. Ideal for contractor-grade residential and multi-family spaces.

Benefits

- Entry level price point for plastic A19 dimmable

Features

- Plastic bulb
- Dimmable
- Lifetime up to 15,000 hours

Application

- Residential
- Multi-family housing




Contractor-grade Plastic (Dimmable) A-Shape Lamps

Versions



LEDbulbE A19 E26 FR

Dimensional drawing



Product	D	C
11A19/CNG/827/FR/P/E26/D 12/1CT	60 mm	106 mm
11A19/CNG/830/FR/P/E26/D 12/1CT	60 mm	106 mm
11A19/CNG/840/FR/P/E26/D 12/1CT	60 mm	106 mm
11A19/CNG/850/FR/P/E26/D 12/1CT	60 mm	106 mm

Product	D	C
14A19/CNG/827/FR/P/E26/D 12/1CT	60 mm	117 mm
14A19/CNG/830/FR/P/E26/D 12/1CT	60 mm	117 mm
14A19/CNG/840/FR/P/E26/D 12/1CT	60 mm	117 mm
14A19/CNG/850/FR/P/E26/D 12/1CT	60 mm	117 mm

Product	D	C
5A19/CNG/827/FR/P/E26/D 12/1CT	60 mm	104 mm
5A19/CNG/830/FR/P/E26/D 12/1CT	60 mm	104 mm
5A19/CNG/840/FR/P/E26/D 12/1CT	60 mm	104 mm
5A19/CNG/850/FR/P/E26/D 12/1CT	60 mm	104 mm
8.8A19/CNG/827/FR/P/E26/D 12/1CT	60 mm	104 mm
8.8A19/CNG/830/FR/P/E26/D 12/1CT	60 mm	104 mm
8.8A19/CNG/840/FR/P/E26/D 12/1CT	60 mm	104 mm
8.8A19/CNG/850/FR/P/E26/D 12/1CT	60 mm	104 mm

Contractor-grade Plastic (Dimmable) A-Shape Lamps

General Information	
Cap-Base	E26
Switching Cycle	50,000
Nominal lifetime	15,000 hour(s)
Light Technical	
Beam Angle (Nom)	180 degree(s)
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A19
Approval and Application	
Ambient temperature range	-20 to +45 °C

Light Technical

		Correlated Color		
Order Code	Full Product Name	Temperature (Nom)	Color Code	Luminous Flux
929003751764	11A19/CNG/827/FR/P/E26/D 12/1CT	2700 K	827	1,100 lm
929003751864	11A19/CNG/830/FR/P/E26/D 12/1CT	3000 K	830	1,100 lm
929003751964	11A19/CNG/840/FR/P/E26/D 12/1CT	4000 K	840	1,100 lm
929003752064	11A19/CNG/850/FR/P/E26/D 12/1CT	5000 K	850	1,100 lm
929003579564	8.8A19/CNG/827/FR/P/E26/D 12/1CT	2700 K	827	800 lm
929003579664	8.8A19/CNG/850/FR/P/E26/D 12/1CT	5000 K	850	800 lm
929003584864	8.8A19/CNG/830/FR/P/E26/D 12/1CT	3000 K	830	800 lm
929003584964	8.8A19/CNG/840/FR/P/E26/D 12/1CT	4000 K	840	800 lm
929003750964	5A19/CNG/827/FR/P/E26/D 12/1CT	2700 K	827	450 lm
929003751064	5A19/CNG/830/FR/P/E26/D 12/1CT	3000 K	830	450 lm
929003751164	5A19/CNG/840/FR/P/E26/D 12/1CT	4000 K	840	450 lm
929003751264	5A19/CNG/850/FR/P/E26/D 12/1CT	5000 K	850	450 lm
929003585064	14A19/CNG/827/FR/P/E26/D 12/1CT	2700 K	827	1,500 lm
929003585164	14A19/CNG/830/FR/P/E26/D 12/1CT	3000 K	830	1,500 lm
929003585264	14A19/CNG/840/FR/P/E26/D 12/1CT	4000 K	840	1,500 lm
929003585364	14A19/CNG/850/FR/P/E26/D 12/1CT	5000 K	850	1,500 lm

Operating and Electrical

		Power	Wattage
Order Code	Full Product Name	Consumption	Equivalent
929003751764	11A19/CNG/827/FR/P/E26/D 12/1CT	11 W	75 W
929003751864	11A19/CNG/830/FR/P/E26/D 12/1CT	11 W	75 W
929003751964	11A19/CNG/840/FR/P/E26/D 12/1CT	11 W	75 W
929003752064	11A19/CNG/850/FR/P/E26/D 12/1CT	11 W	75 W
929003579564	8.8A19/CNG/827/FR/P/E26/D 12/1CT	8.8 W	60 W
929003579664	8.8A19/CNG/850/FR/P/E26/D 12/1CT	8.8 W	60 W
929003584864	8.8A19/CNG/830/FR/P/E26/D 12/1CT	8.8 W	60 W
929003584964	8.8A19/CNG/840/FR/P/E26/D 12/1CT	8.8 W	60 W

		Power	Wattage
Order Code	Full Product Name	Consumption	Equivalent
929003750964	5A19/CNG/827/FR/P/E26/D 12/1CT	5 W	40 W
929003751064	5A19/CNG/830/FR/P/E26/D 12/1CT	5 W	40 W
929003751164	5A19/CNG/840/FR/P/E26/D 12/1CT	5 W	40 W
929003751264	5A19/CNG/850/FR/P/E26/D 12/1CT	5 W	40 W
929003585064	14A19/CNG/827/FR/P/E26/D 12/1CT	14 W	100 W
929003585164	14A19/CNG/830/FR/P/E26/D 12/1CT	14 W	100 W
929003585264	14A19/CNG/840/FR/P/E26/D 12/1CT	14 W	100 W
929003585364	14A19/CNG/850/FR/P/E26/D 12/1CT	14 W	100 W



Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929003751764	11A19/CNG/827/FR/P/E26/D 12/1CT	105 °C
929003751864	11A19/CNG/830/FR/P/E26/D 12/1CT	105 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929003751964	11A19/CNG/840/FR/P/E26/D 12/1CT	105 °C
929003752064	11A19/CNG/850/FR/P/E26/D 12/1CT	105 °C

Contractor-grade Plastic (Dimmable) A-Shape Lamps

Order Code	Full Product Name	T-Case Maximum (Nom)
929003579564	8.8A19/CNG/827/FR/P/E26/D 12/1CT	90 °C
929003579664	8.8A19/CNG/850/FR/P/E26/D 12/1CT	90 °C
929003584864	8.8A19/CNG/830/FR/P/E26/D 12/1CT	90 °C
929003584964	8.8A19/CNG/840/FR/P/E26/D 12/1CT	90 °C
929003750964	5A19/CNG/827/FR/P/E26/D 12/1CT	90 °C
929003751064	5A19/CNG/830/FR/P/E26/D 12/1CT	90 °C
929003751164	5A19/CNG/840/FR/P/E26/D 12/1CT	90 °C
929003751264	5A19/CNG/850/FR/P/E26/D 12/1CT	90 °C
929003585064	14A19/CNG/827/FR/P/E26/D 12/1CT	100 °C
929003585164	14A19/CNG/830/FR/P/E26/D 12/1CT	100 °C
929003585264	14A19/CNG/840/FR/P/E26/D 12/1CT	100 °C
929003585364	14A19/CNG/850/FR/P/E26/D 12/1CT	100 °C



Contractor-grade Plastic (Dimmable) A-Shape Lamps

