



For your everyday lighting jobs

CorePro LEDtube InstantFit HF T5

CorePro LEDtube InstantFit HF T5 is the quick and easy way to replace T5 fluorescent tubes with a fast payback time. Designed with industry leading ballast compatibility, the product is ideal for your everyday lighting jobs. With simply plug-and-play installation, it improves energy efficiency immediately and lasts for longer than conventional T5.

Benefits

- Simple, fast, plug and play retrofit of conventional T5
- Immediate energy savings up to 50%
- Longer lifetime and reduced maintenance cycle

Features


- Retrofit solution with long lifetime of 15.000hrs
- Up to 60% of energy saving
- Instant on, no flicker or buzz
- Enable implementation of HACCP, supported by product level NSF certificate
- No mercury

Application

- Office, school
- Retail
- Industry, warehouse

CorePro LEDtube InstantFit HF T5

Dimensional drawing



Product	D1	D2	A1	A2	A3
CorePro LEDtube HF 1200mm HE 17.1W 830T5	15.5 mm	16/19 mm	1,149 mm	1,156 mm	1,163 mm
CorePro LEDtube HF 1200mm HE 17.1W 840T5	15.5 mm	16/19 mm	1,149 mm	1,156 mm	1,163 mm
CorePro LEDtube HF 1200mm HE 17.1W 865T5	15.5 mm	16/19 mm	1,149 mm	1,156 mm	1,163 mm
CorePro LEDtube HF 1200mm HO 26.7W 830T5	15.5 mm	16/19 mm	1,149 mm	1,156 mm	1,163 mm
CorePro LEDtube HF 1200mm HO 26.7W 840T5	15.5 mm	16/19 mm	1,149 mm	1,156 mm	1,163 mm
CorePro LEDtube HF 1200mm HO 26.7W 865T5	15.5 mm	16/19 mm	1,149 mm	1,156 mm	1,163 mm
CorePro LEDtube HF 1500mm HE 20.5W 830T5	15.5 mm	16/19 mm	1,449 mm	1,456 mm	1,463 mm
CorePro LEDtube HF 1500mm HE 20.5W 840T5	15.5 mm	16/19 mm	1,449 mm	1,456 mm	1,463 mm
CorePro LEDtube HF 1500mm HE 20.5W 865T5	15.5 mm	16/19 mm	1,449 mm	1,456 mm	1,463 mm
CorePro LEDtube HF 1500mm HO 26.7W 830T5	15.5 mm	16/19 mm	1,449 mm	1,456 mm	1,463 mm
CorePro LEDtube HF 1500mm HO 26.7W 840T5	15.5 mm	16/19 mm	1,449 mm	1,456 mm	1,463 mm
CorePro LEDtube HF 1500mm HO 26.7W 865T5	15.5 mm	16/19 mm	1,449 mm	1,456 mm	1,463 mm
CorePro LEDtube HF 600mm HE 7.1W 830T5	15.5 mm	16/19 mm	549 mm	556 mm	563 mm
CorePro LEDtube HF 600mm HE 7.1W 840T5	15.5 mm	16/19 mm	549 mm	556 mm	563 mm
CorePro LEDtube HF 600mm HE 7.1W 865T5	15.5 mm	16/19 mm	549 mm	556 mm	563 mm

CorePro LEDtube InstantFit HF T5

General Information	
Cap-Base	G5
Switching Cycle	50,000
Nominal lifetime	50,000 hour(s)
Light Technical	
Beam Angle (Nom)	200 degree(s)
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Starting Time (Nom)	0.5 s
Temperature	
T-Case Maximum (Nom)	45 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	T5
Approval and Application	
Ambient temperature range	-20 to +45 °C

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color Code	Luminous Flux
929003774102	CorePro LEDtube HF 600mm HE 7.1W 830T5	3000 K	830	1,000 lm
929003774202	CorePro LEDtube HF 600mm HE 7.1W 840T5	4000 K	840	1,050 lm
929003774302	CorePro LEDtube HF 600mm HE 7.1W 865T5	6500 K	865	1,050 lm
929003774702	CorePro LEDtube HF 1500mm HE 20.5W 830T5	3000 K	830	2,800 lm
929003774802	CorePro LEDtube HF 1500mm HE 20.5W 840T5	4000 K	840	3,000 lm
929003774902	CorePro LEDtube HF 1500mm HE 20.5W 865T5	6500 K	865	3,000 lm
929003775302	CorePro LEDtube HF 1500mm HO 26.7W 830T5	3000 K	830	3,700 lm
929003775402	CorePro LEDtube HF 1500mm HO 26.7W 840T5	4000 K	840	3,900 lm
929003775502	CorePro LEDtube HF 1500mm HO 26.7W 865T5	6500 K	865	3,900 lm
929003774402	CorePro LEDtube HF 1200mm HE 17.1W 830T5	3000 K	830	2,300 lm
929003774502	CorePro LEDtube HF 1200mm HE 17.1W 840T5	4000 K	840	2,500 lm
929003774602	CorePro LEDtube HF 1200mm HE 17.1W 865T5	6500 K	865	2,500 lm
929003775002	CorePro LEDtube HF 1200mm HO 26.7W 830T5	3000 K	830	3,700 lm
929003775102	CorePro LEDtube HF 1200mm HO 26.7W 840T5	4000 K	840	3,900 lm
929003775202	CorePro LEDtube HF 1200mm HO 26.7W 865T5	6500 K	865	3,900 lm

Operating and Electrical



Order Code	Full Product Name	Input Frequency	Power Consumption
929003774102	CorePro LEDtube HF 600mm HE 7.1W 830T5	30K to 100K Hz	7.1 W
929003774202	CorePro LEDtube HF 600mm HE 7.1W 840T5	30K to 100K Hz	7.1 W
929003774302	CorePro LEDtube HF 600mm HE 7.1W 865T5	30K to 100K Hz	7.1 W
929003774702	CorePro LEDtube HF 1500mm HE 20.5W 830T5	30K to 100K Hz	20.5 W
929003774802	CorePro LEDtube HF 1500mm HE 20.5W 840T5	30K to 100K Hz	20.5 W
929003774902	CorePro LEDtube HF 1500mm HE 20.5W 865T5	30K to 100K Hz	20.5 W
929003775302	CorePro LEDtube HF 1500mm HO 26.7W 830T5	20K to 140K Hz	26.7 W
929003775402	CorePro LEDtube HF 1500mm HO 26.7W 840T5	20K to 140K Hz	26.7 W

Order Code	Full Product Name	Input Frequency	Power Consumption
929003775502	CorePro LEDtube HF 1500mm HO 26.7W 865T5	20K to 140K Hz	26.7 W
929003774402	CorePro LEDtube HF 1200mm HE 17.1W 830T5	30K to 100K Hz	17.1 W
929003774502	CorePro LEDtube HF 1200mm HE 17.1W 840T5	30K to 100K Hz	17.1 W
929003774602	CorePro LEDtube HF 1200mm HE 17.1W 865T5	30K to 100K Hz	17.1 W
929003775002	CorePro LEDtube HF 1200mm HO 26.7W 830T5	30K to 60K Hz	26.7 W
929003775102	CorePro LEDtube HF 1200mm HO 26.7W 840T5	30K to 60K Hz	26.7 W
929003775202	CorePro LEDtube HF 1200mm HO 26.7W 865T5	30K to 60K Hz	26.7 W



CorePro LEDtube InstantFit HF T5

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929003774102	CorePro LEDtube HF 600mm HE 7.1W 830T5	8 kWh
929003774202	CorePro LEDtube HF 600mm HE 7.1W 840T5	8 kWh
929003774302	CorePro LEDtube HF 600mm HE 7.1W 865T5	8 kWh
929003774702	CorePro LEDtube HF 1500mm HE 20.5W 830T5	21 kWh
929003774802	CorePro LEDtube HF 1500mm HE 20.5W 840T5	21 kWh
929003774902	CorePro LEDtube HF 1500mm HE 20.5W 865T5	21 kWh
929003775302	CorePro LEDtube HF 1500mm HO 26.7W 830T5	27 kWh
929003775402	CorePro LEDtube HF 1500mm HO 26.7W 840T5	27 kWh
929003775502	CorePro LEDtube HF 1500mm HO 26.7W 865T5	27 kWh
929003774402	CorePro LEDtube HF 1200mm HE 17.1W 830T5	18 kWh
929003774502	CorePro LEDtube HF 1200mm HE 17.1W 840T5	18 kWh
929003774602	CorePro LEDtube HF 1200mm HE 17.1W 865T5	18 kWh
929003775002	CorePro LEDtube HF 1200mm HO 26.7W 830T5	27 kWh
929003775102	CorePro LEDtube HF 1200mm HO 26.7W 840T5	27 kWh
929003775202	CorePro LEDtube HF 1200mm HO 26.7W 865T5	27 kWh



CorePro LEDtube InstantFit HF T5



CorePro LEDtube InstantFit HF T5

