



Akcesoria do modułów oświetleniowych i sterowników do oświetlenia ekspozycji w sklepach

Accessories

Sterowniki i akcesoria, które umożliwiają stworzenie kompletnego systemu

Cechy

- Kable
- Zatrzaski
- Profile
- Szynoprzewody
- Inne

Zastosowanie

- Rzeczywista konfiguracja systemu z modułami Integrate G4 i sterownikami o stałym napięciu.
- Rzeczywista konfiguracja systemu z modułami Integrate S i sterownikami o stałym napięciu.
- Rzeczywista konfiguracja systemu z modułami CertaFlux i sterownikami o stałym napięciu.

Wersje



Clip Shelf Arm




IntegrateS Mounting Profile 1200




Integrate engine lock inline




Integrate engine clip mullion center



Integrate mounting clip canopy



Integrate profile 2000mm



Fortimo LEDFlex connector



Integrate engine clip mullion side





Integrate track cable 0.7mG






IntegrateS Mounting Profile 900

Wersje

	InteGrade power cable 1m black		InteGrade cable 2.5m black
	InteGrade track 1200mm G		InteGrade profile 1175mm
	Fortimo LEDFlex connector wire250mm		InteGrade spacer cable 113mm white
	InteGrade connector		InteGrade engin mounting clip G2
			InteGrade spacer cable 0.5m white
			Fortimo LEDFlex cornerconnect wire150mm

Wersje

	InteGrade power cable 2.5m white		InteGrade profile 2000mm Fstyle
	Clip Cannopy 30		Fortimo LEDFlex connector wire2000mm
			InteGrade mounting clip under shelf
	InteGrade cable 2.5m white		Clip Cannopy 0
	InteGrade power cable 2.5m black		InteGrade cable 1m black
	InteGrade engine clip magnetic		InteGrade power cable 1m white

Accessories

Wersje



InteGrade track cable M0.7mG
angle




IntegradeS Mounting Clip



InteGrade mounting clip Tstyle
profile



InteGrade spacer cable 0.5m black



Clip Shelf Front



Fortimo LEDFlex connector
wire500mm



InteGrade cable 1m white



InteGrade profile 875mm




Fortimo LEDFlex cornerconnect
wire60mm

Wersje


Clip Shelf Magnetic




Rysunki techniczne



Product	C1	A1	B1
InteGrade profile 1175mm(46")	11,9 mm	1 175,0 mm	22,2 mm
InteGrade profile 2000mm(79")	11,9 mm	2 000,0 mm	22,2 mm
InteGrade profile 875mm(34")	11,9 mm	875,0 mm	22,2 mm




Product	C1	A1	B1	B2
InteGrade profile 2000mm(79") F style	11,9 mm	2 000,0 mm	31,0 mm	26,0 mm




Product	A1	B1	C1	D1
InteGrade engine lock inline	18,7 mm	10 mm	10,7 mm	4,2 mm


Rysunki techniczne




Product	A1	B1	C1	D1
InteGrade mounting clip for T style prof	66,5 mm	19,5 mm	5 mm	4,2 mm



Product	A
InteGrade cable 1m(39") black angle	1 000 mm
InteGrade cable 1m(39") white angle	1 000 mm
InteGrade cable 2.5m(98") black angle	2 500 mm
InteGrade cable 2.5m(98") white angle	2 500 mm




Product	A
InteGrade spacer cable 0.5m black	500 mm
InteGrade spacer cable 0.5m white	500 mm



Product	A
InteGrade power cable 1m(39") black	1 000 mm
InteGrade power cable 1m(39") white	1 000 mm
InteGrade power cable 2.5m(98") black	2 500 mm
InteGrade power cable 2.5m(98") white	2 500 mm

Rysunki techniczne



Product	C1	A1	B1
InteGrade mounting clip under shelf	12,5 mm	47,0 mm	30,5 mm

