



Accesorii pentru module de iluminat Retail Display și balasturi

Accesorii

Balasturi și accesorii care permit propunerea unui sistem veritabil

Caracteristici

- Cabluri
- Cleme
- Profiluri
- Sistem de șine
- Altele

Cerere

- Propunerea unui sistem veritabil cu module Integrate G4 și balasturi de tensiune constantă.
- Propunerea unui sistem veritabil cu module Integrate S și balasturi de tensiune constantă.
- Propunerea unui sistem veritabil cu module CertaFlux și balasturi de tensiune constantă.

Versions




Clip Shelf Arm



InteGradeS Mounting Profile 1200




InteGrade spacer cable 0.3m black



InteGrade engine lock inline




InteGrade track cable 0.5mT




InteGrade profile 2000mm



InteGrade mounting clip canopy



Fortimo LEDFlex connector



InteGrade track 1800mm G



InteGrade track cable 0.7mG

Versions



IntegrateS Mounting Profile 900



InteGrade cable 2.5m black



Fortimo LEDFlex connector
wire250mm







InteGrade connector



Fortimo LEDFlex cornerconnect
wire150mm

Versions

	InteGrade power cable 2.5m white		InteGrade profile 2000mm Fstyle
	Clip Cannopy 30		Fortimo LEDFlex connector wire2000mm
			InteGrade mounting clip under shelf
	InteGrade cable 2.5m white		Clip Cannopy 0
	InteGrade power cable 2.5m black		InteGrade engine clip magnetic
	InteGrade power cable 6m white		InteGrade power cable 1m white

Versions


IntegrateS Mounting Clip



InteGrade mounting clip Tstyle profile



Clip Shelf Front



Fortimo LEDFlex connector
wire500mm



InteGrade cable 1m white



InteGrade track power cable 1.5m
G




Fortimo LEDFlex cornerconnect
wire60mm




InteGrade magnet Mstyle profile




Clip Shelf Magnetic



Cote




Product	C1	A1	B1
InteGrade profile 1175mm(46")	11,9 mm	1.175,0 mm	22,2 mm
InteGrade profile 2000mm(79")	11,9 mm	2.000,0 mm	22,2 mm



Product	C1	A1	B1	B2
InteGrade profile 2000mm(79") F style	11,9 mm	2.000,0 mm	31,0 mm	26,0 mm


Image
not yet
available

Product
InteGrade magnet for M style profile




Product	A1	B1	C1	D1
InteGrade engine lock inline	18,7 mm	10 mm	10,7 mm	4,2 mm


Cote




Product	A1	B1	C1	D1
InteGrade mounting clip for T style prof	66,5 mm	19,5 mm	5 mm	4,2 mm



Product	A
InteGrade cable 1m(39'') white angle	1.000 mm
InteGrade cable 2.5m(98'') black angle	2.500 mm
InteGrade cable 2.5m(98'') white angle	2.500 mm




Product	A
InteGrade spacer cable 0.5m white	500 mm



Product	A
InteGrade power cable 1m(39'') black	1.000 mm
InteGrade power cable 1m(39'') white	1.000 mm
InteGrade power cable 2.5m(98'') black	2.500 mm
InteGrade power cable 2.5m(98'') white	2.500 mm

Cote



Product	C1	A1	B1
InteGrade mounting clip under shelf	12,5 mm	47,0 mm	30,5 mm

