



# The professional all-in-one LED solution

## FlexFit (Hybrid UL Type A + B) PLC/T

Philips FlexFit (Hybrid UL Type A + B) lamps are designed with the customer in mind for installation flexibility. The FlexFit lamp can operate as both a plug and play (UL Type-A) and direct wire (UL Type-B). As with all Philips products, the FlexFit family of lamps are compatible with more ballasts than any manufacturer giving the customer peace of mind during installation. Additionally, the long life (50K hours) delivers reduced maintenance and replacement costs. Available as replacements for 32W and 42w compact fluorescent lamps

### Benefits

- Simple and fast installations, Type A & Type B
- Reduced operational cost and maintenance cost than conventional lamps
- Fastest and easiest way to upgrade existing luminaires to LED technology

### Features

- All-in-one solution to replace 32w&42w CFL-ni
- Highly energy-efficient
- Easy installation
- Adjustable color temperature
- Long lifetime

### Application

- Retail
- Office
- Hospitality


# FlexFit (Hybrid UL Type A + B) PLC/T

## Versions



Product standard image

## Dimensional drawing



Product	D1	D	A1	A2	A3
16PL-C/T/COR/42HV-5CCT/FF18/4P/10/1	60 mm	60 mm	14 mm	155 mm	171 mm

