



Classic, economical and reliable Highbay

GreenUp Round Highbay SE

GreenUp Round Highbay SE luminaire provides the optimal balance between basic performance and price. The luminaire covers a variety of options, competitive specifications, long term quality and reliability. The range is suitable for most of industrial applications.

Benefits

- Strong energy saving history
- Better and easier on-site calibration
- Robust and reliable with a long service life

Features

- 148 lm/W system efficacy, excellent energy savings and great value for money
- IP65/IK06 protection
- 50k hours lifetime @Ta 35 °C
- -20 °C to 45 °C working temperature

Application

- General manufacturing
- Warehouses
- Logistic centers

GreenUp Round Highbay SE

Dimensional drawing

General Information	
Driver included	Yes
Light source replaceable	No
Light Technical	
Color rendering index (CRI)	>80
Luminous Efficacy (rated) (Nom)	150 lm/W
Luminous Flux	20,000 lm
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	135 W
Controls and Dimming	
Dimmable	-
Mechanical and Housing	
Housing Color	Gray
Ingress protection code	IP65
Approval and Application	
Ambient temperature range	-20 °C to 45 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)
919406022181	BY518P SE LED200/CW PSU WB BR	6500 K
919406022191	BY518P SE LED200/NW PSU WB BR	4000 K

